


Premium
Switches and Sockets



make the
switch


:hager

**Design, though often quite technical,
is first and foremost about emotions:
seeing, understanding, feeling and
experiencing. That's why at Hager,
our goal is above all to put a 'face'
to our products: one of balance,
serenity, elegance and refinement.**

“We must create products that not only reflect that we care, but reflect our philosophy and brand identity”

Erwin van Handenhoven


finesse



Our architecturally inspired finesse range is sure to impress audiences with its minimalistic and precise design, and is considered to be ingeniously simplistic.

finesse	
Switch Plates	10
Switches	11
Sockets	13
Covers only	14

allure



The refined translucent edge that surrounds allure, accentuates its elegant profile – only 9mm off the wall surface, creating a unique floating effect.

allure	
Switch Plates	17
Switches	18
Sockets	20
Covers only	21


silhouette



With a simple and elegant form based on the serene balance of proportions and the reduction of the object essentials, our silhouette range gives each product the right tone of voice in order to fit within its environment.

silhouette	
Switch Plates and Switches	24
Sockets, Electronic Push Button & Cooker Switches	25
Covers only	26

premiere



Quietly boasting functionality and a beautifully understated form, premiere has a simple and stylish look that creates a soothing effect on its surroundings.

premiere	
Switch Plates	30
Switches	31
Architrave Switches and Other Products	32
IP66 Switches	33
Single Sockets	34
Double and 4 Sockets	35

A quality finish right down to the wire

Fingerprint resistant



For maximum lustre, our metal covers have a treated surface to reduce fingerprint marks.

UV stabilised



Strong impact resistant polycarbonate material will not 'yellow' over time.

Slim profile



With a thickness of only 4mm off the wall surface, silhouette and finesse has the lowest profile on the market.

Standard 16AX mech



All of our standard mechanisms will handle a true 16AX fluorescent load.

Extensive research with architects, interior designers, electrical contractors and consumers have created a dynamic, fully featured range of switches and sockets - with an array of styles, colours and finishes to suit any space.

Child safe shutters



A spring loaded shutter protects little fingers from live parts inside sockets.

Roto-loc® mechanism



The patented Roto-loc system eliminates the possibility of the mechanism being pushed back into the wall cavity.

IP2X compliance



Provided with either a retained hinged cap in allure or deep screw receptor with finesse or silhouette for faster installation.

Added value



A full range of accessories and mechs including electronic push buttons and dimmers are also available.

finesse
minimal,
sleek



GOOD
DESIGN
AWARD®
WINNER




Colour range



Gloss White



Matt Black (MB)



Matt White (MW)




Features


- Multiple mounting holes
- Supplied with standard 32mm tapered point fixing screws
- No mechanism push back
- High impact, high gloss UV stabilised polycarbonate construction
- Spray matt finishes available in matt white and matt black
- Screw retention
- Hybrid plates for non-Hager Roto-loc mechanisms



WBQSP4



WBQSPB



WBQSPCE-MW

Switch Plates - No Mechanisms

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	10	★ WBQSP1
	● Matt Black	10	★ WBQSP1-MB
	○ Matt White	10	★ WBQSP1-MW
2 gang	○ Gloss White	10	★ WBQSP2
	● Matt Black	10	★ WBQSP2-MB
	○ Matt White	10	★ WBQSP2-MW
3 gang	○ Gloss White	10	★ WBQSP3
	● Matt Black	10	★ WBQSP3-MB
	○ Matt White	10	★ WBQSP3-MW
4 gang	○ Gloss White	10	★ WBQSP4
	● Matt Black	10	★ WBQSP4-MB
	○ Matt White	10	★ WBQSP4-MW
5 gang	○ Gloss White	10	★ WBQSP5
	● Matt Black	10	★ WBQSP5-MB
	○ Matt White	10	★ WBQSP5-MW
6 gang	○ Gloss White	10	★ WBQSP6
	● Matt Black	10	★ WBQSP6-MB
	○ Matt White	10	★ WBQSP6-MW
Blank	○ Gloss White	10	★ WBQSPB
	● Matt Black	10	★ WBQSPB-MB
	○ Matt White	10	★ WBQSPB-MW
Brush cable entry plate	○ Gloss White	5	★ WBQSPCE
	● Matt Black	5	★ WBQSPCE-MB
	○ Matt White	5	★ WBQSPCE-MW



WBQHSP1



WBQHSP4

Switch Plates - Hybrid (For use with non-Hager mechanisms)

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	10	★ WBQHSP1
	● Matt Black	10	★ WBQHSP1-MB
	○ Matt White	10	★ WBQHSP1-MW
2 gang	○ Gloss White	10	★ WBQHSP2
	● Matt Black	10	★ WBQHSP2-MB
	○ Matt White	10	★ WBQHSP2-MW
3 gang	○ Gloss White	10	★ WBQHSP3
	● Matt Black	10	★ WBQHSP3-MB
	○ Matt White	10	★ WBQHSP3-MW
4 gang	○ Gloss White	10	★ WBQHSP4
	● Matt Black	10	★ WBQHSP4-MB
	○ Matt White	10	★ WBQHSP4-MW


Features

- Multiple mounting holes
- Supplied with captive 32mm tapered point fixing screws
- No mechanism push back
- High impact, high gloss UV stabilised polycarbonate construction
- Press mechs 10A
- Spray matt finishes available in matt white and matt black
- Switch when supplied are fitted with 16AX mechanisms (suitable for fluorescent loads)
- 2 way and loop terminal as standard
- Combination head screws 'backed off' for ease of cable insertion
- Terminals accommodate 4 x 1.5mm² cable
- Push button mechanical switches rated 10A
- 240V press button mechs - 10AX



Switches

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	10	★ WBQSV1
	● Matt Black	10	★ WBQSV1-MB
	○ Matt White	10	★ WBQSV1-MW
2 gang	○ Gloss White	10	★ WBQSV2
	● Matt Black	10	★ WBQSV2-MB
	○ Matt White	10	★ WBQSV2-MW
3 gang	○ Gloss White	5	★ WBQSV3
	● Matt Black	5	★ WBQSV3-MB
	○ Matt White	5	★ WBQSV3-MW
4 gang	○ Gloss White	5	★ WBQSV4
	● Matt Black	5	★ WBQSV4-MB
	○ Matt White	5	★ WBQSV4-MW
5 gang	○ Gloss White	5	★ WBQSV5
	● Matt Black	5	★ WBQSV5-MB
	○ Matt White	5	★ WBQSV5-MW
6 gang	○ Gloss White	5	★ WBQSV6
	● Matt Black	5	★ WBQSV6-MB
	○ Matt White	5	★ WBQSV6-MW




WBQSV1



WBQSV4-MB

Switches with 240V Press Mech

Description	Characteristics	Available colours	Box qty	Cat ref.
1 gang	10AX	○ Gloss White	5	★ WBQSV1PB
		● Matt Black	5	★ WBQSV1PB-MB
		○ Matt White	5	★ WBQSV1PB-MW
2 gang	10AX	○ Gloss White	5	★ WBQSV2PB
		● Matt Black	5	★ WBQSV2PB-MB
		○ Matt White	5	★ WBQSV2PB-MW
3 gang	10AX	○ Gloss White	5	★ WBQSV3PB
		● Matt Black	5	★ WBQSV3PB-MB
		○ Matt White	5	★ WBQSV3PB-MW
4 gang	10AX	○ Gloss White	5	★ WBQSV4PB
		● Matt Black	5	★ WBQSV4PB-MB
		○ Matt White	5	★ WBQSV4PB-MW
240V LED for PB mech LED - blue (Not supplied with switches)	240V		20	★ WBAPBLED



WBQSV1PB

Features

- Multiple mounting holes
- Supplied with captive 32mm tapered point fixing screws
- No mechanism push back
- High impact, high gloss UV stabilised polycarbonate construction
- Spray matt finishes available in matt white and matt black
- Switch when supplied are fitted with 16AX mechanisms (suitable for fluorescent loads)
- 2 way and loop terminal as standard
- Terminals accommodate 4 x 1.5mm² cable
- Combination head screws Phillip's #1 'backed off' for ease of cable insertion

Cooker switch features

- Double pole
- Comes with 2 covers
- One marked with 'cooker'
- One with no marking
- Terminals accept 6mm² cable



WBQSA2

Architrave Switches

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	10	★ WBQSA1
	● Matt Black	10	★ WBQSA1-MB
	○ Matt White	10	★ WBQSA1-MW
2 gang	○ Gloss White	10	★ WBQSA2
	● Matt Black	10	★ WBQSA2-MB
	○ Matt White	10	★ WBQSA2-MW
3 gang	○ Gloss White	5	★ WBQSA3
	● Matt Black	5	★ WBQSA3-MB
	○ Matt White	5	★ WBQSA3-MW



WBQCKSV1

Switches - Vertical Cooker Switch

Description	Characteristics	Available colours	Box qty	Cat ref.
Vertical cooker switch Double pole	40A, 2 Pole	○ Gloss White	1	★ WBQCKSV1
		● Matt Black	1	★ WBQCKSV1-MB
		○ Matt White	1	★ WBQCKSV1-MW



WBQCKSH1

Switches - Horizontal Cooker Switch

Description	Characteristics	Available colours	Box qty	Cat ref.
Horizontal cooker switch Double pole	40A, 2 Pole	○ Gloss White	1	★ WBQCKSH1
		● Matt Black	1	★ WBQCKSH1-MB
		○ Matt White	1	★ WBQCKSH1-MW

Features

- Removable covers for ease of painting
- Multiple mounting holes
- Terminal screws "backed off"
- Bevelled and colour coded cable entries aligned for ease of termination
- Supplied with retained tapered point 32mm fixing screws
- Spray matt finishes available in matt white and matt black

Technical data

- All sockets 250V 50Hz rated
- Extra switch models fitted with 16AX mechanisms
- Terminal accommodates 4 x 2.5mm² cable
- High impact, high gloss UV stabilised polycarbonate construction

Sockets - horizontal

Description	Characteristics	Available colours	Box qty	Cat ref.
Single sockets	10A	○ Gloss White	10	★ WBQP1S
		● Matt Black	10	★ WBQP1S-MB
		○ Matt White	10	★ WBQP1S-MW
	10A 'Round Earth'	○ Gloss White	10	★ WBQP1R
		● Matt Black	10	★ WBQP1R-MB
		○ Matt White	10	★ WBQP1R-MW
	15A	○ Gloss White	5	★ WBQP115S
		● Matt Black	5	★ WBQP115S-MB
		○ Matt White	5	★ WBQP115S-MW
Double sockets	10A	○ Gloss White	10	★ WBQP2S
		● Matt Black	10	★ WBQP2S-MB
		○ Matt White	10	★ WBQP2S-MW
Double sockets with extra switch	10A	○ Gloss White	10	★ WBQP2XS
		● Matt Black	10	★ WBQP2XS-MB
		○ Matt White	10	★ WBQP2XS-MW
Double sockets blanked extra switch	10A	○ Gloss White	10	★ WBQP2XSB
		● Matt Black	10	★ WBQP2XSB-MB
		○ Matt White	10	★ WBQP2XSB-MW
Double sockets with USB Type A and Type C	10A	○ Gloss White	1	★ WBQP2SUSBAC
		● Matt Black	1	★ WBQP2SUSBAC-MB
		○ Matt White	1	★ WBQP2SUSBAC-MW



WBQP2S



WBQP2S-MB



WBQP2SUSBAC

Sockets - vertical

Description	Characteristics	Available colours	Box qty	Cat ref.
Single socket	10A	○ Gloss White	10	★ WBQP1VS
		● Matt Black	10	★ WBQP1VS-MB
		○ Matt White	10	★ WBQP1VS-MW




WBQP1VS

Features

- High impact, high gloss UV stabilised polycarbonate
- Spray matt finishes available in matt white and matt black




WBQCV1




WBQCV4

Switch Cover Plates

Description	Available colours	Box qty	Cat ref.
1 gang	Gloss White	10	★ WBQCV1
	Matt Black	10	★ WBQCV1-MB
	Matt White	10	★ WBQCV1-MW
2 gang	Gloss White	10	★ WBQCV2
	Matt Black	10	★ WBQCV2-MB
	Matt White	10	★ WBQCV2-MW
3 gang	Gloss White	10	★ WBQCV3
	Matt Black	10	★ WBQCV3-MB
	Matt White	10	★ WBQCV3-MW
4 gang	Gloss White	10	★ WBQCV4
	Matt Black	10	★ WBQCV4-MB
	Matt White	10	★ WBQCV4-MW
5 gang	Gloss White	10	★ WBQCV5
	Matt Black	10	★ WBQCV5-MB
	Matt White	10	★ WBQCV5-MW
6 gang	Gloss White	10	★ WBQCV6
	Matt Black	10	★ WBQCV6-MB
	Matt White	10	★ WBQCV6-MW



WBQCP1



WBQCP2XS-MB

Socket Cover Plates - horizontal

Description	Available colours	Box qty	Cat ref.
Cover single socket	Gloss White	5	★ WBQCP1
	Matt Black	5	★ WBQCP1-MB
	Matt White	5	★ WBQCP1-MW
Cover double socket	Gloss White	5	★ WBQCP2
	Matt Black	5	★ WBQCP2-MB
	Matt White	5	★ WBQCP2-MW
Cover double socket with extra switch	Gloss White	5	★ WBQCP2XS
	Matt Black	5	★ WBQCP2XS-MB
	Matt White	5	★ WBQCP2XS-MW



WBQCPV1

Socket Cover Plates - vertical

Description	Available colours	Box qty	Cat ref.
Cover single socket	Gloss White	5	★ WBQCPV1
	Matt Black	5	★ WBQCPV1-MB
	Matt White	5	★ WBQCPV1-MW




allure
authentic,
honest



GOOD
DESIGN
AWARD®
WINNER



Colour range



Gloss White



Matt Black (MB)



Matt White (MW)


Features

- Multiple mounting holes
- Supplied with standard 32mm fixing screws
- No mechanism push back
- High impact, high gloss UV stabilised polycarbonate construction
- Spray matt finishes available in matt white and matt black
- Level to assist installation
- Hinged IP2x caps
- Screw retention




Switch Plates - No Mechanisms

Description	Available colours	Box qty	Cat ref.
1 gang	<input type="radio"/> Gloss White	10	★ WBHSP1
	<input checked="" type="radio"/> Matt Black	10	★ WBHSP1-MB
	<input type="radio"/> Matt White	10	★ WBHSP1-MW
2 gang	<input type="radio"/> Gloss White	10	★ WBHSP2
	<input checked="" type="radio"/> Matt Black	10	★ WBHSP2-MB
	<input type="radio"/> Matt White	10	★ WBHSP2-MW
3 gang	<input type="radio"/> Gloss White	10	★ WBHSP3
	<input checked="" type="radio"/> Matt Black	10	★ WBHSP3-MB
	<input type="radio"/> Matt White	10	★ WBHSP3-MW
4 gang	<input type="radio"/> Gloss White	10	★ WBHSP4
	<input checked="" type="radio"/> Matt Black	10	★ WBHSP4-MB
	<input type="radio"/> Matt White	10	★ WBHSP4-MW
5 gang	<input type="radio"/> Gloss White	10	★ WBHSP5
	<input checked="" type="radio"/> Matt Black	10	★ WBHSP5-MB
	<input type="radio"/> Matt White	10	★ WBHSP5-MW
6 gang	<input type="radio"/> Gloss White	10	★ WBHSP6
	<input checked="" type="radio"/> Matt Black	10	★ WBHSP6-MB
	<input type="radio"/> Matt White	10	★ WBHSP6-MW
Blank	<input type="radio"/> Gloss White	5	★ WBHSPB
	<input checked="" type="radio"/> Matt Black	5	★ WBHSPB-MB
	<input type="radio"/> Matt White	5	★ WBHSPB-MW
Brush cable entry	<input type="radio"/> Gloss White	5	★ WBHSPCE
	<input checked="" type="radio"/> Matt Black	5	★ WBHSPCE-MB
	<input type="radio"/> Matt White	5	★ WBHSPCE-MW



WBHSP1




WBHSP6




WBHSPCE-MW

Switch Plates - Hybrid

Description	Available colours	Box qty	Cat ref.
1 gang	<input type="radio"/> Gloss White	10	★ WBHHSP1
	<input checked="" type="radio"/> Matt Black	10	★ WBHHSP1-MB
	<input type="radio"/> Matt White	10	★ WBHHSP1-MW
2 gang	<input type="radio"/> Gloss White	10	★ WBHHSP2
	<input checked="" type="radio"/> Matt Black	10	★ WBHHSP2-MB
	<input type="radio"/> Matt White	10	★ WBHHSP2-MW
3 gang	<input type="radio"/> Gloss White	10	★ WBHHSP3
	<input checked="" type="radio"/> Matt Black	10	★ WBHHSP3-MB
	<input type="radio"/> Matt White	10	★ WBHHSP3-MW
4 gang	<input type="radio"/> Gloss White	10	★ WBHHSP4
	<input checked="" type="radio"/> Matt Black	10	★ WBHHSP4-MB
	<input type="radio"/> Matt White	10	★ WBHHSP4-MW



WBHHSP1



WBHHSP4

Features

- Multiple mounting holes
- Supplied with captive 32mm fixing screws
- No mechanism push back
- High impact, high gloss UV stabilised polycarbonate construction
- Level to assist installation
- Spray matt finishes available in matt white and matt black
- Switch when supplied are fitted with 16AX mechanisms (suitable for fluorescent loads)
- 2 way and loop terminal as standard
- Hinged IP2x caps
- Combination head screws Phillip's #1 'backed off' for ease of cable insertion
- Terminals accommodate 4 x 1.5mm² cable



WBHSV1



WBHSV1-MB

Switches

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	10	★ WBHSV1
	● Matt Black	10	★ WBHSV1-MB
	○ Matt White	10	★ WBHSV1-MW
2 gang	○ Gloss White	10	★ WBHSV2
	● Matt Black	10	★ WBHSV2-MB
	○ Matt White	10	★ WBHSV2-MW
3 gang	○ Gloss White	5	★ WBHSV3
	● Matt Black	5	★ WBHSV3-MB
	○ Matt White	5	★ WBHSV3-MW
4 gang	○ Gloss White	5	★ WBHSV4
	● Matt Black	5	★ WBHSV4-MB
	○ Matt White	5	★ WBHSV4-MW
5 gang	○ Gloss White	5	★ WBHSV5
	● Matt Black	5	★ WBHSV5-MB
	○ Matt White	5	★ WBHSV5-MW
6 gang	○ Gloss White	5	★ WBHSV6
	● Matt Black	5	★ WBHSV6-MB
	○ Matt White	5	★ WBHSV6-MW



WBHSA2

Switches - Architrave

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	5	★ WBHSA1
	● Matt Black	5	★ WBHSA1-MB
	○ Matt White	5	★ WBHSA1-MW
2 gang	○ Gloss White	5	★ WBHSA2
	● Matt Black	5	★ WBHSA2-MB
	○ Matt White	5	★ WBHSA2-MW
3 gang	○ Gloss White	5	★ WBHSA3
	● Matt Black	5	★ WBHSA3-MB
	○ Matt White	5	★ WBHSA3-MW

Features

- Multiple mounting holes
- Supplied with captive 32mm tapered point fixing screws
- No mechanism push back
- High impact, high gloss UV stabilised polycarbonate construction
- Level to assist installation
- Spray matt finishes available in matt white and matt black

- 2 way and loop terminal as standard
- Combination head screws Phillip's #1 'backed off' for ease of cable insertion
- Hinged IP2x caps
- Terminals accommodate 4 x 1.5mm² cable

Cooker switch features

- Double pole
- Comes with 2 covers
 - One marked with 'cooker'
 - One with no marking
- Terminals accept 6mm² cable



IP44 Switches - vertical


Description	Characteristics	Available colours	Box qty	Cat ref.
1 gang	10A	Gloss White	10	★ WBHWSV1
		Matt Black	10	★ WBHWSV1-MB
		Matt White	10	★ WBHWSV1-MW
2 gang	10A	Gloss White	10	★ WBHWSV2
		Matt Black	10	★ WBHWSV2-MB
		Matt White	10	★ WBHWSV2-MW
3 gang	10A	Gloss White	10	★ WBHWSV3
		Matt Black	10	★ WBHWSV3-MB
		Matt White	10	★ WBHWSV3-MW



WBHWSV1

IP44 Switches - horizontal

Description	Characteristics	Available colours	Box qty	Cat ref.
1 gang	10A	Gloss White	10	★ WBHWSH1
		Matt Black	10	★ WBHWSH1-MB
		Matt White	10	★ WBHWSH1-MW
2 gang	10A	Gloss White	10	★ WBHWSH2
		Matt Black	10	★ WBHWSH2-MB
		Matt White	10	★ WBHWSH2-MW
3 gang	10A	Gloss White	10	★ WBHWSH3
		Matt Black	10	★ WBHWSH3-MB
		Matt White	10	★ WBHWSH3-MW



WBHWSH1

Switches - Vertical Cooker Switch


Description	Characteristics	Available colours	Box qty	Cat ref.
Vertical cooker switch Double pole	40A, 2 Pole	Gloss White	1	★ WBHCKSV1
		Matt Black	1	★ WBHCKSV1-MB
		Matt White	1	★ WBHCKSV1-MW



WBHCKSV1

Switches - Horizontal Cooker Switch

Description	Characteristics	Available colours	Box qty	Cat ref.
Horizontal cooker switch Double pole	40A, 2 Pole	Gloss White	1	★ WBHCKSH1
		Matt Black	1	★ WBHCKSH1-MB
		Matt White	1	★ WBHCKSH1-MW



WBHCKSH1

Features

- Removable covers for ease of painting
- Multiple mounting holes
- Terminal screws "backed off"
- Level to assist installation
- Bevelled and colour coded cable entries aligned for ease of termination
- Supplied with retained tapered point 32mm fixing screws
- Hinged IP2x caps
- Spray matt finishes available in matt white and matt black

Technical data

- All sockets 250V 50Hz rated
- Extra switch models fitted with 16AX mechanisms
- High impact, high gloss UV stabilised polycarbonate construction
- Terminal accommodates 4 x 2.5mm² cable



WBHP2S



WBHP2S-MB



WBHP2SUSBAC-MW

Sockets - horizontal


Description	Characteristics	Available colours	Box qty	Cat ref.
Single sockets	10A	Gloss White	10	★ WBHP1S
		Matt Black	10	★ WBHP1S-MB
		Matt White	10	★ WBHP1S-MW
	10A 'Round Earth'	Gloss White	10	★ WBHP1R
		Matt Black	10	★ WBHP1R-MB
		Matt White	10	★ WBHP1R-MW
	15A	Gloss White	5	★ WBHP115
		Matt Black	5	★ WBHP115-MB
		Matt White	5	★ WBHP115-MW
Double sockets	20A	Gloss White	5	★ WBHP120
		Matt Black	5	★ WBHP120-MB
		Matt White	5	★ WBHP120-MW
	10A	Gloss White	10	★ WBHP2S
		Matt Black	10	★ WBHP2S-MB
		Matt White	10	★ WBHP2S-MW
	Double sockets with extra 16AX switch	Gloss White	10	★ WBHP2XS
		Matt Black	10	★ WBHP2XS-MB
		Matt White	10	★ WBHP2XS-MW
Double sockets with extra switch position (no mech)	10A	Gloss White	10	★ WBHP2XSB
		Matt Black	10	★ WBHP2XSB-MB
		Matt White	10	★ WBHP2XSB-MW
	Double sockets with USB Type A and Type C	Gloss White	1	★ WBHP2SUSBAC
		Matt Black	1	★ WBHP2SUSBAC-MB
		Matt White	1	★ WBHP2SUSBAC-MW



WBHP1V-MB

Sockets - vertical

Description	Characteristics	Available colours	Box qty	Cat ref.
		Gloss White	10	★ WBHP1V
		Matt Black	10	★ WBHP1V-MB
		Matt White	10	★ WBHP1V-MW



WBHA4PP-MB

4 Gang Socket Cover Kit

Description	Characteristics	Available colours	Box qty	Cat ref.
		Gloss White	5	★ WBHA4PP
		Matt Black	5	★ WBHA4PP-MB
		Matt White	5	★ WBHA4PP-MW


Note: 2x allure double sockets (WBHP2S-xx) required (not supplied with kit)

Features


- High impact, high gloss UV stabilised polycarbonate
- Spray matt finishes available in matt white and matt black

Switch Cover Plates

Description	Available colours	Box qty	Cat ref.
1 gang	<input type="radio"/> Gloss White	10	★ WBHCS1
	<input checked="" type="radio"/> Matt Black	10	★ WBHCS1-MB
	<input type="radio"/> Matt White	10	★ WBHCS1-MW
2 gang	<input type="radio"/> Gloss White	10	★ WBHCS2
	<input checked="" type="radio"/> Matt Black	10	★ WBHCS2-MB
	<input type="radio"/> Matt White	10	★ WBHCS2-MW
3 gang	<input type="radio"/> Gloss White	10	★ WBHCS3
	<input checked="" type="radio"/> Matt Black	10	★ WBHCS3-MB
	<input type="radio"/> Matt White	10	★ WBHCS3-MW
4 gang	<input type="radio"/> Gloss White	10	★ WBHCS4
	<input checked="" type="radio"/> Matt Black	10	★ WBHCS4-MB
	<input type="radio"/> Matt White	10	★ WBHCS4-MW
5 gang	<input type="radio"/> Gloss White	10	★ WBHCS5
	<input checked="" type="radio"/> Matt Black	10	★ WBHCS5-MB
	<input type="radio"/> Matt White	10	★ WBHCS5-MW
6 gang	<input type="radio"/> Gloss White	10	★ WBHCS6
	<input checked="" type="radio"/> Matt Black	10	★ WBHCS6-MB
	<input type="radio"/> Matt White	10	★ WBHCS6-MW




WBHCS1




WBHCS4-MB

Socket Cover Plates - horizontal

Description	Available colours	Box qty	Cat ref.
Cover single socket	<input type="radio"/> Gloss White	5	★ WBHCP1
	<input checked="" type="radio"/> Matt Black	5	★ WBHCP1-MB
	<input type="radio"/> Matt White	5	★ WBHCP1-MW
Cover double socket	<input type="radio"/> Gloss White	5	★ WBHCP2
	<input checked="" type="radio"/> Matt Black	5	★ WBHCP2-MB
	<input type="radio"/> Matt White	5	★ WBHCP2-MW
Cover double socket with extra switch	<input type="radio"/> Gloss White	5	★ WBHCP2XS
	<input checked="" type="radio"/> Matt Black	5	★ WBHCP2XS-MB
	<input type="radio"/> Matt White	5	★ WBHCP2XS-MW




WBHCP2-MW



WBHCP2XS-MB

Socket Cover Plates - vertical

Description	Available colours	Box qty	Cat ref.
Cover single socket	<input type="radio"/> Gloss White	5	★ WBHCP1V
	<input checked="" type="radio"/> Matt Black	5	★ WBHCP1V-MB
	<input type="radio"/> Matt White	5	★ WBHCP1V-MW



WBHCP1V-MB



silhouette
**So fine,
just stunning**





Colour range



Gloss White



Matt Black (MB)



Matt White (MW)

Decorative covers



Aluminium (AL)



Stainless Steel (SS)

RotoLoc 
Featured in all switch plates

Features

- Multiple mounting holes
- Supplied with standard 32mm tapered point fixing screws
- No mechanism push back
- High impact high gloss UV stabilised Polycarbonate construction
- 16AX used as standard mechanisms (suitable for fluorescent loads)
- 2 way and loop terminal as standard
- Combination head screws Phillip's #1 'backed off' for ease of cable insertion
- Terminals accommodate 4 x 1.5mm² cable

Switch Plates only - No Mechanisms




























WBSSP4



WBSHSP2



WBSHSP2

Description	Available colours	Box qty	Cat ref.
1 gang	 White	10	WBSSP1
	 Matt Black	10	WBSSP1-MB
	 Matt White	10	WBSSP1-MW
2 gang	 White	10	WBSSP2
	 Matt Black	10	WBSSP2-MB
	 Matt White	10	WBSSP2-MW
3 gang	 White	10	WBSSP3
	 Matt Black	10	WBSSP3-MB
	 Matt White	10	WBSSP3-MW
4 gang	 White	10	WBSSP4
	 Matt Black	10	WBSSP4-MB
	 Matt White	10	WBSSP4-MW
5 gang	 White	10	WBSSP5
	 Matt Black	10	WBSSP5-MB
	 Matt White	10	WBSSP5-MW
6 gang	 White	10	WBSSP6
	 Matt Black	10	WBSSP6-MB
	 Matt White	10	WBSSP6-MW
Blank	 White	5	WBSSPB
Hybrid Plates 2 gang	 White	10	WBSHSP2
	 Matt Black	10	WBSHSP2-MB
	 Matt White	10	WBSHSP2-MW
Hybrid Plates 4 gang	 White	10	WBSHSP4
	 Matt Black	10	WBSHSP4-MB
	 Matt White	10	WBSHSP4-MW



















Switches



WBSSV1-MW



WBSSV1-MB

Description	Available colours	Box qty	Cat ref.
1 gang	 White	10	WBSSV1
	 Matt Black	10	WBSSV1-MB
	 Matt White	10	WBSSV1-MW
2 gang	 White	10	WBSSV2
	 Matt Black	10	WBSSV2-MB
	 Matt White	10	WBSSV2-MW
3 gang	 White	5	WBSSV3
	 Matt Black	5	WBSSV3-MB
	 Matt White	5	WBSSV3-MW
4 gang	 White	5	WBSSV4
	 Matt Black	5	WBSSV4-MB
	 Matt White	5	WBSSV4-MW
5 gang	 White	5	WBSSV5
	 Matt Black	5	WBSSV5-MB
	 Matt White	5	WBSSV5-MW
6 gang	 White	5	WBSSV6
	 Matt Black	5	WBSSV6-MB
	 Matt White	5	WBSSV6-MW

Features

- Removable covers for ease of painting
- Transparent blue mounting grid for easy installation
- Multiple mounting holes
- Terminal screws "backed off"
- Bevelled and colour coded cable entries aligned for ease of termination

- Supplied with standard tapered point 32mm fixing screws

Technical data

- All sockets 250V 50Hz rated
- Extra switch models fitted with 16AX mechanisms
- Hi impact high gloss UV stabilised Polycarbonate construction

- Terminal accommodates 4 x 2.5mm² cable
- Electronic PB switches are 5A

Sockets - horizontal

Description	Characteristics	Available colours	Box qty	Cat ref.
Single sockets	10A	○ White	10	WBSP1S
		● Matt Black	10	WBSP1S-MB
		○ Matt White	10	WBSP1S-MW
	10A 'Round Earth'	○ White	10	WBSP1R
		● Matt Black	10	WBSP1R-MB
	15A	○ White	5	WBSP115S
		● Matt Black	5	WBSP115S-MB
		○ Matt White	5	WBSP115S-MW
Double sockets	10A	○ White	10	WBSP2S
		● Matt Black	10	WBSP2S-MB
		○ Matt White	10	WBSP2S-MW
Double socket with extra switch	10A	○ White	5	WBSP2XS
		● Matt Black	5	WBSP2XS-MB
		○ Matt White	5	WBSP2XS-MW
Double sockets with USB Type A and Type C	10A	○ White	1	★ WBSP2SUSBAC
		● Matt Black	1	★ WBSP2SUSBAC-MB
		○ Matt White	1	★ WBSP2SUSBAC-MW



WBSP2S



WBSP2S-MB

Sockets - vertical

Description	Characteristics	Available colours	Box qty	Cat ref.
Single sockets	10A	○ White	5	WBSP1VS
		● Matt Black	5	WBSP1VS-MB
		○ Matt White	5	WBSP1VS-MW



WBSP1VS

Electronic Push Button Switches

Description	Available colours	Box qty	Cat ref.
1 gang	○ White	1	WBSEV1
2 gang	○ White	1	WBSEV2
3 gang	○ White	1	WBSEV3
4 gang	○ White	1	WBSEV4
5 gang	○ White	1	WBSEV5
6 gang	○ White	1	WBSEV6



WBSEV2

Switches - cooker switch


Description	Available colours	Box qty	Cat ref.
40A cooker switches	○ Gloss White	1	WBSCKSV1
	● Matt Black	1	WBSCKSV1-MB
	○ Matt White	1	WBSCKSV1-MW



WBSCKSV1

Features

- Hi impact high gloss UV stabilised Polycarbonate, real aluminium or real stainless steel construction
- Matt black, white or clear anodized aluminium or brushed stainless steel finish, to reduce finger printing



WBSCV1-MB



WBSCV2-AL

Switch Covers

Description	Available colours	Box qty	Cat ref.
1 gang	Gloss White	5	WBSCV1
	Matt Black	5	WBSCV1-MB
	Matt White	5	WBSCV1-MW
	Aluminium	5	WBSCV1-AL
	Stainless Steel	5	WBSCV1-SS
2 gang	Gloss White	5	WBSCV2
	Matt Black	5	WBSCV2-MB
	Matt White	5	WBSCV2-MW
	Aluminium	5	WBSCV2-AL
	Stainless Steel	5	WBSCV2-SS
3 gang	Gloss White	5	WBSCV3
	Matt Black	5	WBSCV3-MB
	Matt White	5	WBSCV3-MW
	Aluminium	5	WBSCV3-AL
	Stainless Steel	5	WBSCV3-SS
4 gang	Gloss White	5	WBSCV4
	Matt Black	5	WBSCV4-MB
	Matt White	5	WBSCV4-MW
	Aluminium	5	WBSCV4-AL
	Stainless Steel	5	WBSCV4-SS
5 gang	Gloss White	5	WBSCV5
	Matt Black	5	WBSCV5-MB
	Matt White	5	WBSCV5-MW
	Aluminium	5	WBSCV5-AL
	Stainless Steel	5	WBSCV5-SS
6 gang	Gloss White	5	WBSCV6
	Matt Black	5	WBSCV6-MB
	Matt White	5	WBSCV6-MW
	Aluminium	5	WBSCV6-AL
	Stainless Steel	5	WBSCV6-SS
Blank	Matt Black	5	WBSCPB-MB
	Matt White	5	WBSCPB-MW
Special Application Plate Suits WBSSEA2	Aluminium	5	WBSCSEA2-AL
	Stainless Steel	5	WBSCSEA2-SS

Features

- Hi impact high gloss UV stabilised Polycarbonate
- Spray matt finishes available in matt white and matt black

Socket Covers - horizontal

Description	Available colours	Box qty	Cat ref.
Cover single socket	<input type="radio"/> Gloss White	5	WBSCP1
	<input checked="" type="radio"/> Matt Black	5	WBSCP1-MB
	<input type="radio"/> Matt White	5	WBSCP1-MW
	<input type="radio"/> Aluminium	5	WBSCP1-AL
	<input type="radio"/> Stainless Steel	5	WBSCP1-SS
Cover double socket	<input type="radio"/> Gloss White	5	WBSCP2
	<input checked="" type="radio"/> Matt Black	5	WBSCP2-MB
	<input type="radio"/> Matt White	5	WBSCP2-MW
	<input type="radio"/> Aluminium	5	WBSCP2-AL
	<input type="radio"/> Stainless Steel	5	WBSCP2-SS
Cover double socket with extra switch	<input type="radio"/> Gloss White	5	WBSCP2X
	<input checked="" type="radio"/> Matt Black	5	WBSCP2X-MB
	<input type="radio"/> Matt White	5	WBSCP2X-MW
	<input type="radio"/> Aluminium	5	WBSCP2X-AL
	<input type="radio"/> Stainless Steel	5	WBSCP2X-SS



WBSCP2-SS



WBSCP2X-MB

Socket Covers - vertical


Description	Available colours	Box qty	Cat ref.
Cover single socket	<input type="radio"/> Gloss White	5	WBSVCP1
	<input checked="" type="radio"/> Matt Black	5	WBSVCP1-MB
	<input type="radio"/> Aluminium	5	WBSVCP1-AL
	<input type="radio"/> Stainless Steel	5	WBSVCP1-SS



WBSVCP1-AL

premiere

Surround your home in style





Colour range



Gloss White



Black (BK)

Features

- Transparent mounting grid for easy installation
- Multiple mounting holes
- Supplied with standard 32mm tapered point fixing screws
- No mechanism push back
- High impact, high gloss UV stabilised polycarbonate construction
- Removable surrounds for ease of painting



WBSP1



WBSP2-BK

Switch Plates only - No Mechanisms

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	10	WBSP1
	● Black	10	WBSP1-BK
2 gang	○ Gloss White	10	WBSP2
	● Black	10	WBSP2-BK
3 gang	○ Gloss White	10	WBSP3
	● Black	10	WBSP3-BK
4 gang	○ Gloss White	10	WBSP4
	● Black	10	WBSP4-BK
5 gang	○ Gloss White	10	WBSP5
	● Black	10	WBSP5-BK
6 gang	○ Gloss White	10	WBSP6
	● Black	10	WBSP6-BK
Blank	○ Gloss White	10	WBSPB

Features

- Transparent mounting grid for easy installation
- Multiple mounting holes
- Supplied with standard 32mm tapered point fixing screws
- No mechanism push back
- High impact, high gloss UV stabilised polycarbonate construction
- Removable surrounds for ease of painting
- Rocker features in-built arc shield and chemical resistant pivots
- All plates fitted with 16AX mechanisms (suitable for fluorescent loads)
- 2 way and loop terminal as standard
- Combination head screws Phillip's #1 'backed off' for ease of cable insertion
- Terminals accommodate 4 x 1.5mm² cable



Large Plate Switches - vertical

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	10	WBSV1
	● Black	10	WBSV1-BK
2 gang	○ Gloss White	10	WBSV2
	● Black	10	WBSV2-BK
3 gang	○ Gloss White	5	WBSV3
	● Black	5	WBSV3-BK
4 gang	○ Gloss White	5	WBSV4
	● Black	5	WBSV4-BK
5 gang	○ Gloss White	5	WBSV5
	● Black	5	WBSV5-BK
6 gang	○ Gloss White	5	WBSV6
	● Black	5	WBSV6-BK



WBSV1-BK

Large Plate switches - horizontal

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	10	WBSH1
2 gang	○ Gloss White	10	WBSH2
3 gang	○ Gloss White	5	WBSH3



WBSH2

Architrave Switches features

- Supplied with both a premiere and a visage cover for your choice
- Common cover and mounting centres
- Supplied with 12mm tapered point fixing screws

Fan Controller features

- Fan knobs cannot be removed once installed into plate

Card Entry features

- Micro switch controlled
- Supplied with card



WBSA1-BK

Architrave Switches

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	10	WBSA1
	● Black	10	WBSA1-BK
2 gang	○ Gloss White	10	WBSA2
	● Black	10	WBSA2-BK
3 gang	○ Gloss White	5	WBSA3
	● Black	5	WBSA3-BK



WBSF3

Other products

Description	Available colours	Box qty	Cat ref.
Fan controller	○ Gloss White	1	WBSF3
3 speed capacitance 250V 75A	● Black	1	WBSF3-BK
TV plate - PAL 75 OHM	○ Gloss White	10	WBTV75
TV plate - 'F' to 'F' pay TV	○ Gloss White	10	WBTV75PY
Permanent connection plate	○ Gloss White	5	WBPPCU

Features

- Removable surrounds for ease of painting
- Transparent mounting grid for easy installation
- Multiple mounting holes
- Supplied with standard 32mm fixing screws
- High impact, high gloss UV stabilised polycarbonate

IP66 features

- 16A rated mechanism
- 2 way as standard
- Loop terminal as standard
- Terminals take 4 x 1.5mm² cable
- All IP66 switches can be mounted onto the WBBMI for surface mounting

- Designed to ensure IP66 when installed on suitable flat, smooth, non water absorbent surfaces
- Factory sealed IP tested gaskets
- IP rating maintained with sealing plugs in place



IP66 Large Plate Switches - vertical

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	1	WBWSV1
	● Black	1	WBWSV1-BK
2 gang	○ Gloss White	1	WBWSV2
	● Black	1	WBWSV2-BK
3 gang	○ Gloss White	1	WBWSV3
	● Black	1	WBWSV3-BK
4 gang	○ Gloss White	1	WBWSV4
	● Black	1	WBWSV4-BK
3 gang with Light/Fan/Heat printed mechs	○ Gloss White	1	WBWSV3LFH
	● Black	1	WBWSV3LFH-BK
4 gang with Light/Fan/Heat/Heat printed mechs	○ Gloss White	1	WBWSV4LFHH
	● Black	1	WBWSV4LFHH-BK



WBWSV3LFH



WBWSV4LFHH-BK

IP66 Large Plate Switches - horizontal

Description	Available colours	Box qty	Cat ref.
1 gang	○ Gloss White	1	WBWSH1
	● Black	1	WBWSH1-BK
2 gang	○ Gloss White	1	WBWSH2
	● Black	1	WBWSH2-BK
3 gang	○ Gloss White	1	WBWSH3
	● Black	1	WBWSH3-BK
4 gang	○ Gloss White	1	WBWSH4
	● Black	1	WBWSH4-BK
3 gang with Light/Fan/Heat printed mechs	○ Gloss White	1	WBWSH3LFH
	● Black	1	WBWSH3LFH-BK
4 gang with Light/Fan/Heat/Heat printed mechs	○ Gloss White	1	WBWSH4LFHH
	● Black	1	WBWSH4LFHH-BK



WBWSH3LFH



WBWSH4LFHH-BK

Features

- Common cover
- Removable covers for ease of painting
- Transparent mounting grid for easy installation
- Multiple mounting holes
- Terminal screws "backed off"
- Bevelled and colour coded cable entries aligned for ease of termination
- Supplied with standard tapered point 32mm fixing screws

Technical data

- All sockets 250V 50Hz rated
- Extra switch models fitted with 16AX mechanisms
- High impact, high gloss UV stabilised polycarbonate construction
- Terminal accommodates 4 x 2.5mm² cable



WBP1S



WBP115S-BK

Single Sockets - horizontal

Description	Available colours	Box qty	Cat ref.
10A	○ Gloss White	10	WBP1S
	● Black	10	WBP1S-BK
15A	○ Gloss White	5	WBP115S
	● Black	5	WBP115S-BK
20A	○ Gloss White	5	WBP120
10A double pole	○ Gloss White	10	WBP1DS
15A	○ Gloss White	5	WBP115DS
10A with extra switch	○ Gloss White	5	WBP1XS
	● Black	5	WBP1XS-BK
10A with 2 extra switches	○ Gloss White	5	WBP1XXS
	● Black	5	WBP1XXS-BK
10A with round earth pin	○ Gloss White	5	WBP1R
	● Black	5	WBP1R-BK



WBP1VS



WBP1VXS-BK

Single Sockets - vertical

Description	Available colours	Box qty	Cat ref.
10A	○ Gloss White	5	WBP1VS
	● Black	5	WBP1VS-BK
	● Red	5	WBP1VS-RD
15A	○ Gloss White	5	WBP115VS
	● Black	5	WBP115VS-BK
10A with extra switch	○ Gloss White	5	WBP1VXS
	● Black	5	WBP1VXS-BK
10A with 2 extra switches	○ Gloss White	5	WBP1VXXS
	● Black	5	WBP1VXXS-BK

Features

- Common cover
- Removable covers for ease of painting
- Transparent mounting grid for easy installation
- Multiple mounting holes
- Terminal screws "backed off"
- Bevelled and colour coded cable entries aligned for ease of termination
- Supplied with standard tapered point 32mm fixing screws
- 4 outlet sockets have same mounting centres as double socket outlets.

Technical data

- All sockets 250V 50Hz rated with 16AX mechanisms
- Extra switch models fitted with 16AX mechanisms
- High impact high gloss UV stabilised polycarbonate construction
- Terminal accommodates 4 x 2.5mm² cable

Double Sockets - horizontal

Description	Available colours	Box qty	Cat ref.
10A	○ Gloss White	10	WBP2S
	● Black	10	WBP2S-BK
	● Red	10	WBP2S-RD
10A double pole	○ Gloss White	10	WBP2DS
10A with extra switch	○ White	5	WBP2XS
	● Black	5	WBP2XS-BK
10A with circuit id	○ Gloss White	10	WBP2CID
	● Black	10	WBP2CID-BK
Double sockets + USB Type A and C	○ Gloss White	1	WBP2SUSBAC



WBP2S

Double Sockets - vertical

Description	Available colours	Box qty	Cat ref.
10A	○ Gloss White	10	WBP2VS
	● Black	10	WBP2VS-BK
10A with extra switch	○ Gloss White	5	WBP2VXS
	● Black	5	WBP2VXS-BK



WBP2VS

4 Outlet Sockets - horizontal

Description	Available colours	Box qty	Cat ref.
10A	○ Gloss White	4	WBP4S
	● Black	4	WBP4S-BK
10A with extra switch	○ Gloss White	4	WBP4XS
	● Black	4	WBP4XS-BK



WBP4S



WBP4XS

Complete the picture



Modules, mechanisms and accessories

Mechanisms - Electronic Push Buttons and Dimmers	38
Mechanisms - 250V	39
Mechanisms - 250V Printed	40
Mechanisms - 250V Rotary	41
Mechanisms - TV, Data and Audio	42
Mechanisms - Special Mechanisms	43
Accessories	44
Weatherproof Switches and Sockets	46
Weatherproof Isolators - IP66	47

Features:

- Slave Push Button Switch available
- All electronic mechanisms are EMC compliant
- Supplied with White, Matt Black and Matt White caps or rotary knob



WBME5A

Electronic Push Button Switch Mechanism

Description	Available colours	Box qty	Cat ref.
230/240V AC 1200W	○ White Complete with MB and MW interchangeable coloured caps	5	WBME5A



WBMDUPB

Electronic Push Button Universal Dimmer Mechanism

Description	Available colours	Box qty	Cat ref.
250W - LED loads 300W - Incandescent loads	○ White Complete with MB and MW interchangeable coloured caps	5	★ WBMDUPB



WBMDUR

Electronic Universal Rotary Dimmer Mechanism

Description	Available colours	Box qty	Cat ref.
250W - LED loads 300W - Incandescent loads	○ White Complete with MB and MW knobs	5	★ WBMDUR



WBMSLL

Electronic Push Button Slave Mechanism

Description	Available colours	Box qty	Cat ref.
To be used only in conjunction with either WBMDUPB, WBMDUR or WBME5A.	○ White Complete with MB and MW interchangeable coloured caps	5	★ WBMSLL



WBAEDB

Dimmer Caps and Knobs

Description	Available colours	Cat ref.
Dimmer caps for WBMDUPB and WBMSLL	○ Gloss White	★ WBAEDB
	● Gloss Black	★ WBAEDB-BK
	● Matt Black	★ WBAEDB-MB
	○ Matt White	★ WBAEDB-MW
Dimmer knob for WBMDUR	○ Gloss White	★ WBAEDK
	● Gloss Black	★ WBAEDK-BK
	● Matt Black	★ WBAEDK-MB
	○ Matt White	★ WBAEDK-MW



WBAEDK-MB

Features

- Easy mechanism removal
- Rear housing colour coded for easy recognition of mechanism type
- All terminal screws are combination head Phillips No. 1 and backed off

Technical data:

- 3mm contact gap in WBM16AX
- All 250V mechanism's have M60 motor rating
- 32A and 20AX mechanism 'socket size' terminal accommodates 2 x 4mm² cables
- Intermediate and double pole have 75% of terminal screws accessible from 1 direction
- Terminals accommodate 4 x 1.5mm² cables
- Push mech rated at 10A
- Tactile mech rated 6A



250V PB Mechanisms

Description	Available colours	Box qty	Cat ref.
LED for push button	○ Blue	20	★ WBAPBLED
10AX flush push button - 2 way	○ White	5	★ WBMPB
	● Matt Black	5	★ WBMPB-MB
	○ Matt White	5	★ WBMPB-MW
6AX 240V push button tactile/momentary mech (Available early 2022)	○ White	5	★ WBMTPB
	● Matt Black	5	★ WBMTPB-MB
	○ Matt White	5	★ WBMTPB-MW



WBMPB

250V Mechanisms

Description	Available colours	Box qty	Cat ref.
16A AX rated STANDARD	○ White	5	WBM16AX
	● Black	5	WBM16AX-BK
	○ Matt White	5	WBM16AX-MW
	● Matt Black	5	WBM16AX-MB
	● Red	5	WBM16AX-RD
20A Standard	○ White	5	WBM20
	● Black	5	WBM20-BK
	○ Matt White	5	WBM20-MW
	● Matt Black	5	WBM20-MB
16A AX rated with lens	○ White	5	WBM16AXL
	● Black	5	WBM16AXL-BK
16A AX rated with neon light	○ White	5	WBM16AXN
10A double pole	○ White	5	WBM10D
	● Black	5	WBM10D-BK
	○ Matt White	5	WBM10D-MW
	● Matt Black	5	WBM10D-MB
10A intermediate	○ White	5	WBM10I
	● Black	5	WBM10I-BK
	○ Matt White	5	WBM10I-MW
	● Matt Black	5	WBM10I-MB
20A AX rated 1 way only	○ White	5	WBM20AX
	● Black	5	WBM20AX-BK
	○ Matt White	5	WBM20AX-MW
	● Matt Black	5	WBM20AX-MB
32A 1 way only	○ White	5	WBM32
	● Black	5	WBM32-BK
	○ Matt White	5	WBM32-MW
	● Matt Black	5	WBM32-MB
15A press	○ White	5	WBM15P
	○ Matt White	5	WBM15P-MW
	● Matt Black	5	WBM15P-MB
15A without printed "press"	○ White	5	WBM15PB
	○ Matt White	5	WBM15PB-MW
	● Matt Black	5	WBM15PB-MB



WBM16AX
Standard Mechanism



WBM16AXL



WBM16AXN



WBM10D-MB



WBM10I-MB



WBM15P-MB

Features

- Easy mechanism removal
- Rear housing colour coded for easy recognition of mechanism type
- All terminal screws are combination head Phillips No. 1 and backed off

Technical data

- 3mm contact gap in WBM16AX
- All 250V mechanism's have M60 motor rating
- Intermediate and double pole have 75% of terminal screws accessible from 1 direction
- 10A, 16AX and 20A terminals accommodate 4 x 1.5mm² cables
- Push mech rated at 10A
- 32A and 20AX mechanism 'socket size' terminal accommodates 2 x 4mm² cables



WBM16L



WBM20F



WBM20H



WBM32HO



WBM32O

250V Printed Mechanisms

Description	Available colours	Box qty	Cat ref.
'LIGHT' 16A AX 2 way	○ White	5	WBM16L
	● Black	5	WBM16L-BK
	○ Matt White	5	WBM16L-MW
	● Matt Black	5	WBM16L-MB
'FAN' 20A 1 way	○ White	5	WBM20F
	● Black	5	WBM20F-BK
	○ Matt White	5	WBM20F-MW
	● Matt Black	5	WBM20F-MB
'HEAT' 20A 1 way	○ White	5	WBM20H
	● Black	5	WBM20H-BK
	○ Matt White	5	WBM20H-MW
	● Matt Black	5	WBM20H-MB
'HOT WATER' 20A 1 way	○ White	5	WBM20HW
'HOT WATER' 32A 1 way	● Matt Black	5	WBM32HW-MB
	○ Matt White	5	WBM32HW-MW
'SENSOR' 20A 1 way	○ White	5	WBM20SN
'HOB' 32A 1 way	○ White	5	WBM32HO
	● Black	5	WBM32HO-BK
	○ Matt White	5	WBM32HO-MW
	● Matt Black	5	WBM32H-MB
'OVEN' 32A 1 way	○ White	5	WBM32O
	● Black	5	WBM32O-BK
	○ Matt White	5	WBM32O-MW
	● Matt Black	5	WBM32O-MB
'RANGE' 32A 1 way	○ White	5	WBM32R
	● Black	5	WBM32R-BK
	○ Matt White	5	WBM32R-MW
	● Matt Black	5	WBM32R-MB

Feature

- Easy mechanism removal

Technical data

- Terminals accommodate
4 x 1.5mm² cables



250V Rotary Mechanisms

Description	Available colours	Box qty	Cat ref.
10A 3 position rotary	○ White	10	WBM10R3
10A 3 pos. rotary - w/ capacitor (fan)	● Matt Black	10	WBMSF3-MB
	○ Matt White	10	WBMSF3-MW
10A 3 pos. rotary - Auto/Manual	○ White	10	WBM10RAM
10A 3 pos. rotary - Lo/Hi	○ White	10	WBM10RLH
10A 3 pos. rotary - Sensor	○ White	10	WBM10RSN
10A 3 pos. rotary - Up/Down	○ White	10	WBM10RUD
Rotary Knob to suit rotary mechs	○ White	10	WBARK1
	● Black	10	WBARK1-BK
	○ Matt White	10	WBARK1-MW
	● Matt Black	10	WBARK1-MB



WBM10R3



WBARK

Rotoloc Data Mechanisms

- Data Mechs are tested and approved to the following standards where relevant:

ANSI/TIA-568-C.2-2009
ISO/IEC 11801-1
IEC 60603-7-2
AS/CA S008:2015I

Audio Connectors

- RCA jacks have 'F' connection at rear
- Available in multiple colours for maximum installation flexibility
- Speaker connectors suitable for both bare wire termination and banana plugs



WBMTV75PF



WBMTV75PY-MB

TV Mechanisms

Description	Available colours	Box qty	Cat ref.
'F' to PAL type mechanism	○ White	10	WBMTV75PF
	● Black	10	WBMTV75PF-BK
	○ Matt White	10	WBMTV75PF-MW
	● Matt Black	10	WBMTV75PF-MB
TV socket mechanism 3GHz 75Ohm Foxtel approved	○ White	10	WBMTV75PY
	● Black	10	WBMTV75PY-BK
	○ Matt White	10	WBMTV75PY-MW
	● Matt Black	10	WBMTV75PY-MB



WBMCAT6-MW



WBMCAT6A

Rotoloc Data Mechanisms

Description	Available colours	Box qty	Cat ref.
8 Pin Cat5e	○ White	10	WBMCAT5
8 Pin Cat6	○ White	10	WBMCAT6
	● Black	10	WBMCAT6-BK
	○ Matt White	10	WBMCAT6-MW
	● Matt Black	10	WBMCAT6-MB
8 Pin Cat6A	○ White	10	WBMCAT6A



WBMHDMI

Audio Connectors

Description	Available colours	Box qty	Cat ref.
M/M HDMI pass through	○ White	5	WBMHDMI
	● Matt Black	5	WBMHDMI-MB
	○ Matt White	5	WBMHDMI-MW
RCA connectors for composite audio/video - 1 x red, 1 x white, 1 x yellow	○ White	5	WBMRCA1
	● Black	5	WBMRCA1-BK

Circuit ID features:

- Circuit ID cannot be removed from front of plate once installed

Technical data

- Cord grip mechanism will accept light and heavy duty flexible cables
- Circuit ID labels supplied in sheets of 10, A4 size.



Special Mechanisms

Description	Available colours	Box qty	Cat ref.
Cord grip mechanism	○ White	5	WBMPCU
Circuit ID mechanism	○ White	5	WBMCID
Blank mechanism	○ White	5	WBMBP
	● Black	5	WBMBP-BK
ELV tactile mechanism extra low voltage tactile switch momentary contact	○ White	5	WBMLVT
	● Black	5	WBMLVT-BK
	○ Matt White	5	WBMLVT-MW
ELV tactile mechanism + neon extra low voltage tactile switch with LED indication momentary contact	○ White	5	WBMLVTN
	● Black	5	WBMLVTN-BK
	○ Matt White	5	WBMLVTN-MW
	● Matt Black	5	WBMLVTN-MB
Neon lights	250V Neon – red	5	WBM250NRD
	250V Neon – amber	5	WBM250NAM
	250V Neon – green	5	WBM250NGR
	250V Neon – clear	5	WBM250NCL
USB Mechanism 1 x TYPE A 1 x TYPE C	○ White	1	★ WBMUSBAC
	● Black	1	★ WBMUSBAC-BK
	○ Matt White	1	★ WBMUSBAC-MW
	● Matt Black	1	★ WBMUSBAC-MB



WBMCID




WBMBP



WBMLVT



WBMLVTN



WBM250NRD

Special Keystone Data to Rotoloc Adaptors

Description	Available colours	Box qty	Cat ref.
Suits Panduit®	○ White		WBAKAPAN
Suits SYSTIMAX®	○ White		WBAKASYS
Suits general type	○ White		WBAKAGEN

Note: Always check fitting of data mech as some models may vary.



WBAKAPAN



WBAKASYS



WBAKAGEN

Mounting Block features

- Hi Impact UV stabilised Polycarbonate
- Compatible with all large plate switches and sockets

Surface sockets features

- Safety Shroud for extra security and safety.
- Can be tested when fitted to mounting plate



WBBMD



WBSBMD



WBBMI

Mounting Accessories

Description	Available colours	Box qty	Cat ref.
premiere Mounting block 32mm deep	○ White	5	WBBMD
	● Black	5	WBBMD-BK
silhouette mounting block 32mm deep	○ White	5	WBSBMD
	● Matt Black	5	WBSBMD-MB
allure mounting block	○ White	5	★ WBHMBD
	● Matt Black	5	★ WBHMBD-MB
finesse mounting block 84mm interaxe	○ White	5	★ WBQMBD
	● Matt Black	5	★ WBQMBD-MB
premiere Mounting block 18mm deep	○ White	5	WBBMS
premiere Mounting block to suit 4 gang outlet	○ White	4	WBBM4
Insulated back to suit 4 gang mounting block	○ White	8	WBBM4BP
premiere Insulated mounting block 32mm deep	○ White	10	WBBMI
	● Black	10	WBBMI-BK
premiere Surface mounting kit 29mm deep suits premiere plates only	○ White	5	WBBSMK
	● Black	5	WBBSMK-BK
Wall box 1 gang moulded plastic		10	WBBWB



WBAP1

Surface Sockets

Description	Characteristics	Available colours	Box qty	Cat ref.
Single surface sockets	10A	○ White	10	WBAP1
	15A	○ White	10	WBAP115
with round earth pin	10A	○ White	10	WBAP1R
Replacement mounting plate			30	WBAP1MP

Junction Box feature

- Includes quickfix screws and terminal connectors

Shrouds

- Shroud for insulating live parts

Junction Boxes

Description	Available colours	Box qty	Cat ref.
Giant junction box with quick fix screws and 4 cable connectors	○ White	5	WBAJB4
Standard junction box with quick fix screws and 3 cable connectors	○ White	10	WBAJB4S



WBAJB4S

Shrouds and Covers

Description	Box qty	Cat ref.
Insulating shroud size 2 suits premiere products	10	WBBS2
Paint cover suits premiere products only	30	WBAPC



WBBS2

Miscellaneous

Description	Box qty	Cat ref.
M3.5 X 50mm long pan head tapered point mounting screw 50 screws per box	50	WBASC50
Mechanism removal tool		WBMS
Screw connectors - single	100	WBAC1B
Screw connectors - twin	50	WBAC2B



WBASC50



WBAC2B

Description

Our surface mounted range of IP rated switches and sockets are designed for outdoor applications. Easy to install with two single screws fixing the top cover to the base.

Electrical Specification

Switch - 16A, 250V AC
Single pole 2 way with loop
Socket - 10/15A, 250V AC
Single pole

Mechanical specification

- IP66 for switches
- IP53 for sockets
- External material is UV stabilised polycarbonate



WBWS216

Switches

Description	Characteristics	Box qty	Cat ref.
16A IP66 switches	1 gang	1	WBWS116
	2 gang	1	WBWS216



WBWP1S

Single Sockets

Description	Characteristics	Box qty	Cat ref.
IP53 single socket	10A	1	WBWP1S
	15A	1	WBWP115S
IP53 single socket (White)	10A	1	★ WBWP1S-W
	15A	1	★ WBWP115S-W



WBWP2S

10A Double Sockets

Description	Characteristics	Box qty	Cat ref.
10A, IP53 double socket		1	WBWP2S
	shallow mount	1	WBWP2SH
10A, IP53 double socket (White)		1	★ WBWP2S-W
	shallow mount	1	★ WBWP2SH-W



WBWP2SH

Description

Our range of Weatherproof Isolators are designed to be used in indoor or outdoor applications with IP66 degree of protection. They are switch disconnectors for 2, 3 and 4 pole supply, from 20A to 63A. Rated at AC-23A, they can also be used to isolate motor/compressor loads without derating. They provide ample wiring room and are easy to install with a 2 screw quick release top cover.


Electrical Specification

- AS/NZS IEC 60947-3
- Rated voltage:
250V AC 50/60Hz
440V AC 50/60Hz
- Utilization category
AC-21A, AC-22A, AC-23A for
switching any type of load from
resistive to highly inductive loads

Mechanical Specification

- IP66
- External material is UV stabilised polycarbonate
- Ø25mm top and bottom cable entry hole caps
- Ø25mm and Ø20mm conduit entry knock-cuts
- Ø20mm mounting holes
- Handle provides Ø6mm shank padlocking facility (ON & OFF position)


2 pole Isolators

Description	Characteristics	Operational power input			Box qty	Cat ref.
		AC-21A	AC-22A	AC-23A		
IP66 	20A	4.8kW	4.0kW	3.3kW	1	JG220IN
	32A	7.6kW	6.4kW	5.2kW	1	JG232IN
	40A	9.5kW	8.0kW	6.5kW	1	JG240IN
	63A	15kW	12.6kW	10.2kW	1	JG263IN



JG240IN


3 pole Isolators

Description	Characteristics	Operational power input			Box qty	Cat ref.
		AC-21A	AC-22A	AC-23A		
IP66 	20A	14.5kW	12.2kW	9.9kW	1	JG320IN
	32A	23.2kW	19.5kW	15.9kW	1	JG332IN
	40A	29kW	24.4kW	19.8kW	1	JG340IN



JG340IN

4 pole Isolators

Description	Characteristics	Operational power input			Box qty	Cat ref.
		AC-21A	AC-22A	AC-23A		
IP66 N 	20A	14.5kW	12.2kW	9.9kW	1	JG420IN
	32A	23.2kW	19.5kW	15.9kW	1	JG432IN
	40A	29kW	24.4kW	19.8kW	1	JG440IN
	63A	45.6kW	38.4kW	31.2kW	1	JG463IN



JG440IN



Hager Electro Pty Ltd
Unit 17/2-8 South Street
Rydalmere NSW 2116

Phone: 1300 850 253
Fax: 1300 424 372
customerservice@hagerelectro.com.au
hagerelectro.com.au