

Hager Inspire
wiring accessories

Design for a better life

:hager

Milestones of Hager wiring accessories



1919

Berker Brothers began to manufacture the first batch of rotary switches in Schalksmühle. Every detail was as simple, elegant, and functional as all Berker's other subsequent models.



1948

Traditionally, water-proof switches are made of cast resin or ceramics. Therefore, Berker's molded plastics rotary switch is a real innovation. The threads of the rotary switch are pressed into the top of the gland cover and grease cavity seals are installed on the axle. This type of switches features optimal waterproof performance. Its basic design features remained unchanged for decades of years.



1966

Although it seems quite natural today, dating back to 1966, the launch of a switch equipped with a dismountable switch cover that can be backfilled after the completion of the painting engineering indicated a significant innovation and great progress in terms of convenience. Moreover, since the switch cover is easy to change, many of the 1966 rocker switches are still in good keep today and can still work normally.



1980

The combination of circle and square was one of our most successful products in the grim technical environment in the 1980s.



1996

'Twinpoint' design has interchangeable decorative rings, which provides all kinds of design possibilities



1928

Form + Function: When Bauhaus began to carry this concept forward, Berker Brothers have turned to the famous architect Louis Henri Sullivan's design concept. Functional and perfect design combined with reliable technology – Berker's switches already had all the elements that a product needs to become classic. These products later became classic indeed.



1957

The cover of this type of switch is as colorful as any of the modern works of art – That is why this colorful sample is called 'Chagall'.



1972

A big success, where modularization is used, the first type of stainless all-metal switch – Another real innovation.



1983

An expert to deal with difficult tasks: 'ISO-Panzer' has excellent waterproof and shockproof performances excellent waterproof and shockproof performances



1999

TS series can not only assist in creating special lighting effect, but can also combine KNX system for operating the complete smart home system.



2003

Full ranges included system 8000, 9000, 9088 metal ranges for Asia launched.



2008

The greatest feature of TS Crystal Ball is its glittering Swarovski crystal and sensitive optical reflection sensor, very charming.



2009

Touch of style as system 10088 equipped with large rocker and blue LED indication.



2016

Berker Q.7 not only highlights its form, functions, and craftsmanship, but also lifts architectural individuality and material application to a higher level.



2020

Hager Dream, Hager Inspire, Hager Muse with best-in-class aesthetics design, quality and full functions to answer all needs.



2004

Intelligence is a kind of beauty. Undoubtedly, B.I.Q looks very beautiful: The first type of smart and fashionable home control unit in the world indicates the arrival of the new era of comfort.



2007

Only by touching... That is the artistic state to start to control a room. Technical progress makes it possible for us to combine minimalism with modern technology and create a new exchange mode.



2011

R.1 series explains its design of round angle of the excircle in its unique way. It has a soft framework outline and all kinds of functional versions. It is a good choice for all residential and decoration projects.



2013

stylea with slim and nice profile large rocker provided affordable option.




2018

Dream series, designed by the European designer, Erwin van Handenhoven, a winner of many international awards, bring elegant life experience to customers.

A flat-lay composition featuring several white electronic components, including USB-C and USB-A ports, and red lipstick tubes, arranged on a black background. The text "Inspire to aim high" is centered in the image.

**Inspire to
aim high**





**Creative
round
design**





Exquisite design

With fine craft, designed precisely, only for the purpose of providing abundant wiring space and convenient installation means.



Delicate chamfering

Good design lies in every detail. Creative and delicate idea brings excellence to our living and working spaces.

Multicolor options

Many choices to fit your ideas: white, aurora silver, noble bronze, knight black, and elegant gold.





The unique brand

Individuality need not to be displayed but it is an expression of your character. The hager brand is exquisitely and uniquely located on the side, offering the product boundless space for expression and letting the essence of beauty blend with the quality of life.



Consistent in size

In accordance with the highest standard, the switch and socket are consistent in size, offering flexible interchange-ability.



13A 3 pin socket with USB charger

The socket is equipped with two 2.4A USB chargers, which intelligently adapt to mobile devices with different power consumptions, ensuring safety and fast charging.

Multi gang frame

Conjoined switch, socket and data combination, a delight on the wall, convenient and beautiful.



The image is a top-down view of a white surface featuring several custom switch panels. The central panel is black with a white square in the middle containing a circle divided into three vertical segments. Surrounding it are other panels: one with black polka dots, one with orange and blue shapes, one with orange polka dots, one with black and white horizontal stripes, and one with orange and blue shapes. A pair of gold-handled scissors is positioned in the upper right, and a red panel is partially visible on the right edge. The background includes faint geometric lines and letters like 'F', 'H', and 'L'.


Customized panels

To meet design requirements, customers can enjoy exclusive customized service, making your switch panels unique.

A I T H



O R A



Switch equipped with fluorescent indicator

The switch is dotted with rays of light like twinkling stars, waiting quietly for its guests to enter. Responding to your fingertip, it makes the home bright.



IP55 waterproof cover

Ensuring safety against water and dust ingress when operating in wet and dusty areas.



Quick installation

The mounting bracket has superior strength and rigidity. It is suitable for all kinds of installation conditions.

U type screwed terminals

Capacity of terminal can fit 3 x 4mm² flexible/ rigid cable. However, it is easy for wiring and faster for installation.







USB charger

4.2A, 5V charger with 1 Type C and 2 Type A port suits most portable electronic devices. No need for extra charger, with only USB cables. Up to 3 devices can be charged simultaneously. Easy and convenient to use.



16AX reliable and high performance

Mechanical switch

Rated current: 16AX

Rated Power: 4000W

The load capacity of switch is stronger, for better performance in increasing demanding installation.

Identification for power

Delayed power off is built-in, which save power in a smart way. The insert tag switch has LED indicator, which makes it easy for you to find the slot in the dark. After power on, the indicator will turn off automatically.



Hager Inspire series



Hager inspire series	Page
Switches	18-19
Dimmer and fan controller switches	19
Double pole control switches	20
Connection unit	21
5A and 10A socket outlets	22
13A socket outlets	22
15A and 16A socket outlets	23
Communication and data	24
Hotel range	25
Others	26
Product standard	27
Ingress protection	30
Circuit diagram	31
Application	34
Success cases	40

- Complies with IEC 60669-1 CB certificate
- 'AX' rated - No need to derate for fluorescent loads
- 10 AX (100W Self Ballasted Lamp (SBL))
- 16 AX (200W Self Ballasted Lamp (SBL))
- Supplied with M3.5 x 37 mm long fixing screws
- Capacity of each terminal: 3 x 1.5 mm² 2 X 2.5 mm²
- Two way switches can be wired either 1 way or 2 way
- Terminal markings denote: L1 = one way L2 = two way C = common
- Material: Polycarbonate

		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Aurora Silver	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
		Large dolly switch						
WGCL111 WGCL112		16AX, 1 gang 1 way	10	WGCL111	WGCXL111AS	WGCXL111NB	WGCXL111KB	WGCXL111EG
		16AX, 1 gang 2 way	10	WGCL112	WGCXL112AS	WGCXL112NB	WGCXL112KB	WGCXL112EG
WGCL121 WGCL122		16AX, 2 gang 1 way	10	WGCL121	WGCXL121AS	WGCXL121NB	WGCXL121KB	WGCXL121EG
		16AX, 2 gang 2 way	10	WGCL122	WGCXL122AS	WGCXL122NB	WGCXL122KB	WGCXL122EG
		16AX, 3 gang 1 way	10	WGCL131	WGCXL131AS	WGCXL131NB	WGCXL131KB	WGCXL131EG
WGCL131 WGCL132		16AX, 3 gang 2 way	10	WGCL132	WGCXL132AS	WGCXL132NB	WGCXL132KB	WGCXL132EG
		16AX, 4 gang 1 way	10	WGCL141	WGCXL141AS	WGCXL141NB	WGCXL141KB	WGCXL141EG
WGCL141 WGCL142		16AX, 4 gang 2 way	10	WGCL142	WGCXL142AS	WGCXL142NB	WGCXL142KB	WGCXL142EG
		Large dolly switch with fluorescence						
WGCL111F WGCL112F		16AX, 1 gang 1 way	10	WGCL111F	WGCXL111FAS	WGCXL111FNB	WGCXL111FKB	WGCXL111FEG
		16AX, 1 gang 2 way	10	WGCL112F	WGCXL112FAS	WGCXL112FNB	WGCXL112FKB	WGCXL112FEG
WGCL121F WGCL122F		16AX, 2 gang 1 way	10	WGCL121F	WGCXL121FAS	WGCXL121FNB	WGCXL121FKB	WGCXL121FEG
		16AX, 2 gang 2 way	10	WGCL122F	WGCXL122FAS	WGCXL122FNB	WGCXL122FKB	WGCXL122FEG
		16AX, 3 gang 1 way	10	WGCL131F	WGCXL131FAS	WGCXL131FNB	WGCXL131FKB	WGCXL131FEG
WGCL131F WGCL132F		16AX, 3 gang 2 way	10	WGCL132F	WGCXL132FAS	WGCXL132FNB	WGCXL132FKB	WGCXL132FEG
		16AX, 4 gang 1 way	10	WGCL141F	WGCXL141FAS	WGCXL141FNB	WGCXL141FKB	WGCXL141FEG
WGCL141F WGCL142F		16AX, 4 gang 2 way	10	WGCL142F	WGCXL142FAS	WGCXL142FNB	WGCXL142FKB	WGCXL142FEG
		Round switch						
WGCR111 WGCR112		16AX, 1 gang 1 way	10	WGCR111	WGCXR111AS	WGCXR111NB	WGCXR111KB	WGCXR111EG
		16AX, 1 gang 2 way	10	WGCR112	WGCXR112AS	WGCXR112NB	WGCXR112KB	WGCXR112EG
WGCR121 WGCR122		16AX, 2 gang 1 way	10	WGCR121	WGCXR121AS	WGCXR121NB	WGCXR121KB	WGCXR121EG
		16AX, 2 gang 2 way	10	WGCR122	WGCXR122AS	WGCXR122NB	WGCXR122KB	WGCXR122EG
		16AX, 3 gang 1 way	10	WGCR131	WGCXR131AS	WGCXR131NB	WGCXR131KB	WGCXR131EG
WGCR131 WGCR132		16AX, 3 gang 2 way	10	WGCR132	WGCXR132AS	WGCXR132NB	WGCXR132KB	WGCXR132EG
















- Complies with
IEC 60669-1
CB certificate

- 10 AX
(100W Self Ballasted Lamp (SBL))

- Capacity of each terminal:
3 x 1.5 mm²
2 x 2.5 mm²

- Material: polycarbonate

- Supplied with M3.5 x 37 mm
long fixing screws

		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Aurora Sliver	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
								
		Large dolly switch						
		10AX, 1 gang intermediate	10	WGCL113	WGCXL113AS	WGCXL113NB	WGCXL113KB	WGCXL113EG
		10A, 1 gang bell switch mark bell symbol	10	WGCL111B	WGCXL111BAS	WGCXL111BNB	WGCXL111BKB	WGCXL111BEG
		10A, 1 gang press switch mark "EXIT"	10	WGCL111E	WGCXL111EAS	WGCXL111ENB	WGCXL111EKB	WGCXL111EEG
		Press switch						
		10A, 1 gang	10	WGCL111P	WGCXL111PAS	WGCXL111PNB	WGCXL111PKB	WGCXL111PEG
		10A, 2 gang	10	WGCL121P	WGCXL121PAS	WGCXL121PNB	WGCXL121PKB	WGCXL121PEG
		10A, 3 gang	10	WGCL131P	WGCXL131PAS	WGCXL131PNB	WGCXL131PKB	WGCXL131PEG
		10A, 4 gang	10	WGCL141P	WGCXL141PAS	WGCXL141PNB	WGCXL141PKB	WGCXL141PEG
		Press round switch						
		10A, 1 gang	10	WGCR111P	WGCXR111PAS	WGCXR111PNB	WGCXR111PKB	WGCXR111PEG
		10A, 2 gang	10	WGCR121P	WGCXR121PAS	WGCXR121PNB	WGCXR121PKB	WGCXR121PEG
		10A, 3 gang	10	WGCR131P	WGCXR131PAS	WGCXR131PNB	WGCXR131PKB	WGCXR131PEG








Hager Inspire Dimmer and fan controller switches

- Complies with
IEC 60669-2-1

- Supplied with M3.5 x 37 mm
long fixing screws

- Capacity of each terminal:
3 x 1.5 mm²

- Material: Polycarbonate

		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Aurora Sliver	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
								
		Fan control						
		250VA, single	6	WGCEFR250	WGCXEFR250AS	WGCXEFR250NB	WGCXEFR250KB	WGCXEFR250EG
		Dimmer						
		40-500W single, 2 way	6	WGCEDR500	WGCXEDR500AS	WGCXEDR500NB	WGCXEDR500KB	WGCXEDR500EG

Remark 1: Separate ordering for single or twin frame is required for all color ranges; Only white range references come in complete set.

Remark 2: Subject to change without prior notice

- Complies with
IEC 60669-1
CB certificate

- 20 AX
(250W Self Ballasted Lamp (SBL))

- Supplied with M3.5 x 37 mm
long fixing screws

- Capacity of each terminal:

20AX

L, N, E: 2 x 4 mm²

32A, 45A

L, N : 2.5 mm² ~ 16 mm²

E x 2: 2.5 mm² ~ 16 mm²

- Material: Polycarbonate

Description	Pack qty.	Cat. Ref. White	Cat. Ref. Aurora Silver	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
DP switch						
20AX, 1 gang	10	WGCL2D1	WGCXL2D1AS	WGCXL2D1NB	WGCXL2D1KB	WGCXL2D1EG
20AX, 2 gang	10	WGCL2D2	WGCXL2D2AS	WGCXL2D2NB	WGCXL2D2KB	WGCXL2D2EG



WGCL2D1




WGCL2D2

Remark: Grey reference product - coming soon



WGCL2D1N
WGCL2D12N



WGCL2D2N

DP switch with LED

20AX, 1 gang	10	WGCL2D1N	WGCXL2D1NAS	WGCXL2D1NNB	WGCXL2D1NKB	WGCXL2D1NEG
20AX, 2 gang	10	WGCL2D2N	WGCXL2D2NAS	WGCXL2D2NNB	WGCXL2D2NKB	WGCXL2D2NEG
20AX, 1 gang 2 way	10	WGCL2D12N	WGCXL2D12NAS	WGCXL2D12NNB	WGCXL2D12NKB	WGCXL2D12NEG

Special marks	Abbreviation	Special marks	Abbreviation	Special marks	Abbreviation
"AIR CONDITONER"	AC	"HOB"	HB	"WASHER"	WS
"DISH WASHER"	DW	"HOOD"	HD	"WASHING MACHINE"	WM
"DRYER"	DR	"MICROWAVE"	MW	"WATER HEATER"	WH
"FRIDGE"	FR	"OVEN"	OV		

Example: **"WATER HEATER" WH**

20AX 1 gang **WGCL2D1WH WGCXL2D1ASWH WGCXL2D1NBWH WGCXL2D1KBWH WGCXL2D1EGWH**



WGCR32D1



WGCR45D1

Control switch with LED

32A DP	8	WGCR32D1	WGCXR32D1AS	WGCXR32D1NB	WGCXR32D1KB	WGCXR32D1EG
45A DP	8	WGCR45D1	WGCXR45D1AS	WGCXR45D1NB	WGCXR45D1KB	WGCXR45D1EG

Remark: Grey reference product - coming soon

- 25A connection units
Complies with
BS 5733
IEC 60998-1
IEC 60998-2-1

- 13A Fused connection units
Complies with
BS 1363-4

- Supplied with M3.5 x 37 mm
long fixing screws

- Capacity of each terminal:
25A
4 x 2.5 mm² or 2 x 4 mm² or 1 x 6 mm²

13A FCU
L, N : 3 x 4.0 mm²
E : 2 x 4.0 mm²

- Material: polycarbonate



WGCR25

Description	Pack qty.	Cat. Ref. White	Cat. Ref. Aurora Silver	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold

Connection unit

25A with flex outlet	14	WGCR25	WGCXR25AS	WGCXR25NB	WGCXR25KB	WGCXR25EG
-------------------------	----	---------------	------------------	------------------	------------------	------------------

Remark: Grey reference product - coming soon



WGCR13



WGCR13N

Fused connection unit

13A fused w/ flex outlet	10	WGCR13	WGCXR13AS	WGCXR13NB	WGCXR13KB	WGCXR13EG
13A fused w/ LED + flex outlet	10	WGCR13N	WGCXR13NAS	WGCXR13NNB	WGCXR13NKB	WGCXR13NEG
13A switched fused w/ flex outlet	10	WGCR13S	WGCXR13SAS	WGCXR13SNB	WGCXR13SKB	WGCXR13SEG
13A switched fused w/ flex outlet w/ LED	10	WGCR13SN	WGCXR13SNAS	WGCXR13SNNB	WGCXR13SNKB	WGCXR13SNEG

Remark: Grey reference product - coming soon

Hager Inspire

5A and 10A socket outlets



- Complies with
BS 547 (5A sockets)
SS 472 (5A sockets)
IEC 60884-1 (10A socket)

- Supplied with M3.5 x 37 mm
long fixing screws

- Capacity of each terminal:
L, N, E : 3 X 2.5 mm² or
2 X 4.0 mm²

- Integral rocker design of
switched sockets provides
clear red 'on' indication

- Material: Polycarbonate

		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Aurora Silver	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
 WGCS105S	 WGCS110US	Socket outlet						
		5A round pin switched	10	WGCS105S	WGCXS105SAS	WGCXS105SNB	WGCXS105SKB	WGCXS105SEG
		10A 2 pin switched	10	WGCS110US	WGCXS110USAS	WGCXS110USNB	WGCXS110USKB	WGCXS110USEG
 WGCS210U		10A 2 pin +2 pin	10	WGCS210U	WGCXS210UAS	WGCXS210UNB	WGCXS210UKB	WGCXS210UEG

Remark: Grey reference product - coming soon

Hager Inspire

13A socket outlets

- Complies with
BS 1363-2
SS 145-2












- Supplied with M3.5 x 37 mm
long fixing screws

- USB output current
2.4A (Max)

- Material: Polycarbonate










- Capacity of each terminal:
L, N, E : 3 X 2.5 mm² or
2 X 4.0 mm²

- Integral rocker design of
switched sockets provides
clear red 'on' indication

		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Aurora Silver	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold
								
		13A single	10	WGCS113	WGCXS113AS	WGCXS113NB	WGCXS113KB	WGCXS113EG
		13A single switched	10	WGCS113S	WGCXS113SAS	WGCXS113SNB	WGCXS113SKB	WGCXS113SEG
WGCS113	WGCS113S	13A single switched w/ LED	10	WGCS113N	WGCXS113NAS	WGCXS113NNB	WGCXS113NKB	WGCXS113NEG
		13A single switched + 2 x USB chargers	8	WGCS113SUSB	WGCXS113SUSBAS	WGCXS113SUSBNB	WGCXS113SUSBKB	WGCXS113SUSBEG
		13A twin	14	WGCS213	WGCXS213AS	WGCXS213NB	WGCXS213KB	WGCXS213EG
WGCS113N	WGCS113SUSB	13A twin switched	14	WGCS213S	WGCXS213SAS	WGCXS213SNB	WGCXS213SKB	WGCXS213SEG
		13A twin switched w/ LED	14	WGCS213N	WGCXS213NAS	WGCXS213NNB	WGCXS213NKB	WGCXS213NEG
		13A twin switched + 2 x USB chargers	10	WGCS213SUSB	WGCXS213SUSBAS	WGCXS213SUSBNB	WGCXS213SUSBKB	WGCXS213SUSBEG
WGCS213	WGCS213S							
WGCS213N	WGCS213SUSB							

Remark: Grey reference product - coming soon

- Complies with BS 546 (15A sockets)
SS 472 (15A sockets)
IEC 60884-1 (16A German socket)
(Euro-American socket)
- Supplied with M3.5 x 37 mm long fixing screws
- USB output current 2.4A (Max)
- Material: Polycarbonate
- Capacity of each terminal: L, N, E : 3 X 2.5 mm² or 2 X 4.0 mm²
- Integral rocker design of switched sockets provides clear red 'on' indication

		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Aurora Silver	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
								
	WGCS115S	15A round pin switched	10	WGCS115S	WGCXS115SAS	WGCXS115SNB	WGCXS115SKB	WGCXS115SEG
	WGCS116S	16A German socket w/ shutter	8	WGCS116S	WGCXS116SAS	WGCXS116SNB	WGCXS116SKB	WGCXS116SEG
	WGCS116EA	16A single Euro-American	10	WGCS116EA	WGCXS116EAAS	WGCXS116EANB	WGCXS116EAKB	WGCXS116EAEG
	WGCS216EA	16A twin Euro-American	10	WGCS216EA	WGCXS216EAAS	WGCXS216EANB	WGCXS216EAKB	WGCXS216EAEG

Remark: Grey reference product - coming soon

- Supplied with M3.5 x 37 mm
long fixing screws

- Material: Polycarbonate
















		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Aurora Silver	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold
		RJ11 outlet						
		1 mod	10	WGCT1RJ	WGCXT1RJAS	WGCXT1RJNB	WGCXT1RJKB	WGCXT1RJEG
		2 mod	10	WGCT2RJ	WGCXT2RJAS	WGCXT2RJNB	WGCXT2RJKB	WGCXT2RJEG
		RJ45 outlet loose plate						
		1 mod	20	WGCT1RJ6LP	WGCXT1RJ6LPAS	WGCXT1RJ6LPNB	WGCXT1RJ6LPKB	WGCXT1RJ6LPEG
		1 mod without symbol	20	WGCT1RJ6LPNM	WGCXT1RJ6LPNMAS	WGCXT1RJ6LPNMNB	WGCXT1RJ6LPNMKB	WGCXT1RJ6LPNMEG
		2 mod	20	WGCT2RJ6LP	WGCXT2RJ6LPAS	WGCXT2RJ6LPNB	WGCXT2RJ6LPKB	WGCXT2RJ6LPEG
		2 mod without symbol	20	WGCT2RJ6LPNM	WGCXT2RJ6LPNMAS	WGCXT2RJ6LPNMNB	WGCXT2RJ6LPNMKB	WGCXT2RJ6LPNMEG
		RJ45 cat6 outlet						
		1 mod	10	WGCT1RJ6	WGCXT1RJ6AS	WGCXT1RJ6NB	WGCXT1RJ6KB	WGCXT1RJ6EG
		1 mod without symbol	10	WGCT1RJ6NM	WGCXT1RJ6NMAS	WGCXT1RJ6NMNB	WGCXT1RJ6NMKB	WGCXT1RJ6NMEG
		2 mod	10	WGCT2RJ6	WGCXT2RJ6AS	WGCXT2RJ6NB	WGCXT2RJ6KB	WGCXT2RJ6EG
		2 mod without symbol	10	WGCT2RJ6NM	WGCXT2RJ6NMAS	WGCXT2RJ6NMNB	WGCXT2RJ6NMKB	WGCXT2RJ6NMEG
		RJ45 cat5e outlet						
		1 mod	10	WGCT1RJ5	WGCXT1RJ5AS	WGCXT1RJ5NB	WGCXT1RJ5KB	WGCXT1RJ5EG
		2 mod	10	WGCT2RJ5	WGCXT2RJ5AS	WGCXT2RJ5NB	WGCXT2RJ5KB	WGCXT2RJ5EG
		RJ11 + RJ45 cat5e outlet						
		2 mod	10	WGCT2RJRJ5	WGCXT2RJRJ5AS	WGCXT2RJRJ5NB	WGCXT2RJRJ5KB	WGCXT2RJRJ5EG
		RJ11 + RJ45 cat6 outlet						
		2 mod	10	WGCT2RJRJ6	WGCXT2RJRJ6AS	WGCXT2RJRJ6NB	WGCXT2RJRJ6KB	WGCXT2RJRJ6EG
		TV inlet/outlet + RJ45 cat5e						
		2 mod	10	WGCT2TVRJ5	WGCXT2TVRJ5AS	WGCXT2TVRJ5NB	WGCXT2TVRJ5KB	WGCXT2TVRJ5EG
		TV inlet/outlet						
		1 mod	10	WGCT1TV	WGCXT1TVAS	WGCXT1TVNB	WGCXT1TVKB	WGCXT1TVEG
		TV inlet/outlet + R45 cat6 (DATA marking)						
		2 mod	10	WGCT2TVRJ6	WGCXT2TVRJ6AS	WGCXT2TVRJ6NB	WGCXT2TVRJ6KB	WGCXT2TVRJ6EG
		TV outlet, F type						
		1 mod	10	WGCT1TVF	WGCXT1TVFAS	WGCXT1TVFNB	WGCXT1TVFKB	WGCXT1TVFEG
		TV outlet, F type + R45 Cat6 (DATA marking)						
		1 mod	10	WGCT2TVFRJ6	WGCXT2TVFRJ6AS	WGCXT2TVFRJ6NB	WGCXT2TVFRJ6KB	WGCXT2TVFRJ6EG


















- Complies with
IEC 60669-1
IEC 60669-2-1
IEC 62368-1 (USB)

- 10 AX
(100W Self Ballasted Lamp (SBL))

- Supplied with M3.5 x 37 mm
long fixing screws

- Material: Polycarbonate

	Description	Pack qty.	Cat. Ref. White	Cat. Ref. Aurora Silver	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
							
	16AX DND & 10 MUR with LED (Indoor)	10	WGCHDC	WGCXHDCAS	WGCXHDCNB	WGCXHDCKB	WGCXHDCEG
WGCHDC							
	HDMI+VGA	10	WGCHHIVA	WGCXHHIVAAS	WGCXHHIVANB	WGCXHHIVAKB	WGCXHHIVAEG
WGCHHIVA							
	RCA+S-Video socket	10	WGCHRCASV	WGCXHRCASVAS	WGCXHRCASVNB	WGCXHRCASVKB	WGCXHRCASVEG
WGCHRCASV							
	USB charger USB charger 4.2A (1 x type C) + (2 x type A)	8	WGCS3USB	WGCXS3USBAS	WGCXS3USBNB	WGCXS3USBKB	WGCXS3USBEG
WGCS3USB							
	USB + 3.5mm audio	10	WGCHUSB35	WGCXHUSB35AS	WGCXHUSB35NB	WGCXHUSB35KB	WGCXHUSB35EG
WGCHUSB35							
	Emergency switch	8	WGCEE1	WGCXEE1AS	WGCXEE1NB	WGCXEE1KB	WGCXEE1EG
WGCEE1							
	Audio switch 6W	6	WGCEA6	WGCXEA6AS	WGCXEA6NB	WGCXEA6KB	WGCXEA6EG
WGCEA6							
	Shaver socket (with frame for color products) 115/230V	1	WGCHSR	WGCXHSRAS	WGCXHSRNB	WGCXHSRKB	WGCXHSRREG
WGCHSR							
	16A key tag - mechanical	6	WGCHKTM	WGCXHKTMAS	WGCXHKTMB	WGCXHKTMB	WGCXHKTMEG
WGCHKTM							
	16A key tag - RFID	6	WGCHKTRFID	WGCXHKTFRIDAS	WGCXHKTFRIDNB	WGCXHKTFRIDKB	WGCXHKTFRIDEG
WGCHKTRFID							

	Description	Pack qty.	Cat. Ref. White	Cat. Ref. Aurora Silver	Cat. Ref. Noble Bronze	Cat. Ref. Knight Black	Cat. Ref. Elegant Gold
							
Multi-gang frame							
 WGCH2KB	2 gang horizontal	18	WGCH2	WGCH2AS	WGCH2NB	WGCH2KB	WGCH2EG
 WGCV2NB	2 gang vertical	18	WGCV2	WGCV2AS	WGCV2NB	WGCV2KB	WGCV2EG
 WGCH3NB	3 gang horizontal	12	WGCH3	WGCH3AS	WGCH3NB	WGCH3KB	WGCH3EG
 WGCV3	3 gang vertical	12	WGCV3	WGCV3AS	WGCV3NB	WGCV3KB	WGCV3EG
 WGCH4	4 gang horizontal	12	WGCH4	WGCH4AS	WGCH4NB	WGCH4KB	WGCH4EG
 WGCH5KB	5 gang horizontal	9	WGCH5	WGCH5AS	WGCH5NB	WGCH5KB	WGCH5EG
Blank plate							
 WGCBP1	1 gang	20	WGCBP1	WGCBP1AS	WGCBP1NB	WGCBP1KB	WGCBP1EG
Single frame							
 WGCC2	2 gang	25	WGCC2	WGCC2AS	WGCC2NB	WGCC2KB	WGCC2EG
 WGCC1S	1 gang square	40	WGCC1S	WGCC1SAS	WGCC1SNB	WGCC1SKB	WGCC1SEG
 WGCC1R	1 gang round	40	WGCC1R	WGCC1RAS	WGCC1RNB	WGCC1RKB	WGCC1REG
WA covers (Transparent)							
 XC9003	IP55 single size	40	XC9003				
 XC9004	IP55 twin size	40	XC9004				

Compliance with standards

Regulation 511-01-01 of BS 7671 : Requirements for Electrical Installations, IEE Wiring Regulations Sixteenth Edition is of particular importance to specifiers and installers with respect to product standards.

Regulation 511-01-01 requires every item of equipment to comply with the relevant requirements of the applicable British Standard, or Harmonised Standard appropriate to the intended use of the equipment.

British Standards (BS)

The BSI (British Standards Institution) was the first national standards body in the world. There are now more than 100 similar organisations which belong to the International Organisation for Standardisation (ISO) and the International Electrotechnical Commission (IEC).

British Standards are drawn up by all those who have a particular interest in the subject i.e. manufacturers, users, research organisations, government departments and consumers. This work is co-ordinated by BSI staff, acting as secretaries to the committees where the work is done. All standards are made available for public comment before they are published.

Harmonised standards

A Harmonised standard is a European standard formally presented by CENELEC, to the European Commission and published in the commission's official journal. CENELEC is the Comité Européen de Normalisation Electrotechnique i.e. European Committee for Electrotechnical Standardisation.

BS 7671 part 2 defines a harmonised standard as a standard which has been drawn up by common agreement between national standards bodies notified to the European Commission by all member states and published under national procedures. The UK national standards body is the British Standards Institution. In the UK a harmonised standard will normally be published as a British Standard European Norm i.e. BS EN.

British Standard European Norm (BS EN)

CENELEC European standards are pre-fixed EN (European Norm). Adoption of the European Standard within the EC is mandatory and member countries of CENELEC are obliged to publish them unchanged. In the UK such standards are further endorsed with the additional prefix 'BS', for example BS EN 60669-1 : 1996 is the British Standard European Norm for Switches for household and similar fixed electrical installations.

Whilst a European Standard can be a direct replica of an IEC standard, discussions within CENELEC may result in the formulation of a standard which includes commonly agreed variations and Special National Conditions.

International Electrotechnical Commission (IEC)

Founded in 1906 the International Electrotechnical Commission (IEC) is the world organisation that prepares and publishes international standards for all electrical, electronic and related technologies. The membership consists of 60 participating countries, including all the world's major trading nations and a growing number of industrialising countries.

Foreign national standards based on IEC standards are permitted to be used by BS 7671. However the specifier must verify that any differences between the foreign standard and the corresponding British Standard or Harmonised Standard does not result in any lesser degree of safety than that afforded by compliance with the British Standard. This assessment would probably need to be made by specialists.

Conclusion

BS 7671 (IEE Wiring Regulations) recognises equipment which complies with a British Standard or Harmonised Standard appropriate to the intended use of the equipment without the need for further qualification.

Hager products have always been designed and manufactured to a high standard to ensure compliance with the current British or Harmonised Standard. See the table below for further information.

Product description	BS / IEC number	Description
Switches	BS EN 60669-1 IEC 60669-1 CB certificate	Switches for household and similar fixed electrical installations
Indicators	BS 5733	General requirements for Electrical Accessories
Fused connection unit, cord outlets	BS 5733	Switches for household and similar fixed electrical installations with particular requirements for timedelay switches (TDS)
Dimmers	BS EN 60669-2-3	Switches for household and similar fixed electrical installations with particular requirements for timedelay switches (TDS)
Frames and plates	BS 5733	Switches for household and similar fixed electrical installations with particular requirements for timedelay switches (TDS)
10 /16 Amp Wall switch-	BS EN 60669-1 IEC 60669-1 CB certificate	Switches for household and similar fixed electrical installations
Dimmer switches	BS EN 60669-2-1 IEC 60669-2-1	Electronic variable control switches (dimmer switches) for tungsten filament lighting
13 Amp Socket Outlets	BS 1363- 2 SS145-2	13A plugs, socket-outlets, adaptors and connection units
15 Amp Switched Socket	BS 546 SS472 MS1577	Specification. Two-pole and earthing-pin plugs, socket-outlets and socket-outlet adaptors
20 Amp D.P. Switches	BS EN 60669-1 IEC 60669-1 CB certificate	Switches for household and similar fixed electrical installations
13 Amp Fused Connection Unit	BS 1363-4	Specification for 13A fused connection units switched and unswitched
45 Amp D.P. Switches	BS EN 60669-1 IEC 60669-1 CB certificate	Switches for household and similar fixed electrical installations
45 Amp Cooker Control Unit	BS 4177	Cooker control units
Shaver Socket Outlet	BS EN 61558-2-5 IEC 61558-2-5	General Requirements Isolating transformers and safety isolating transformers Electromagnetic compatibility, immunity requirements for household CB certificate appliances tools and similar apparatus.
25 Amp/ Amp Flex Outlet Plate	BS 5733	General Requirements for Electrical Accessories
BS Batten	BS EN 61184 IEC 61184 BS EN 60238 IEC 60238	Home office shield are T2 rated
Ceiling rose	BS 67	

Objective of CE marking.

CE marking is a “technical passport” which indicates that a product conforms to all relevant directives which require CE marking, thus enabling the product to travel within the E.U.

A directive is a piece of mandatory European Legislation implemented by regulations in all member countries. Its purpose is to allow free movement of goods that are safe and fit for use into and within the European Union.

CE marking is not a quality mark and it does not indicate that any testing or certification has been carried out.

The marking.

CE marking is a statement by the manufacturer that the product complies with the essential requirements of all relevant Directives, notably in the area of technical safety and conformity assessment.

CE marking can appear on the product or packaging or documentation or combination thereof dependant upon which directive it has to comply with.

CE marking is a very specific graphical symbol and must be clearly separated from other marks.



Directives.

It is the responsibility of the manufacturer or his authorised representative who places the product onto the EC market to decide which Directive(s) apply and to ensure the CE marking is affixed by the dates stated in the relevant directive(s)

For the majority of Hager products only one directive is applicable this is referred to as the Low Voltage Directive. Where some products incorporate electronic devices the Low voltage Directive and the Electromagnetic Compatibility Directive are applicable.

The low voltage directive.

EC directives are requirements adopted by the European Council and published in the official journal of the European Communities and are addressed to the member states.

European Council Directive 73/23/EEC with an amendment 93/68/EEC is known as the Low Voltage Directive.

The low voltage directive has been implemented into UK law by the “Electrical Equipment (Safety) Regulations 1994” and apply to all electrical / electronic equipment operating at a voltage of 50-1000 V a.c. or 75-1500 V d.c.. They do not apply to plugs, socket outlets and adapters which are covered by the Plugs and Sockets (Safety) Regulations 1994.

Relationship between the Electrical Equipment (Safety)

Regulations, Harmonised standards and the IEE Wiring

Regulations Sixteenth Edition.







The Electrical Equipment (Safety) Regulations requires electrical equipment to be safe. Electrical equipment which satisfies the safety provisions of Harmonised standards shall be taken to comply with this requirement, unless there are reasonable grounds for suspecting that the equipment does not so comply.

Regulation 511-01-01 of BS 7671 Requirements for Electrical Installations, IEE Wiring Regulations Sixteenth Edition requires every item of equipment to comply with the relevant requirements of the applicable British Standard, or Harmonised Standard appropriate to the intended use of the equipment.

The Ingress Protection (IP) for all low voltage enclosures up to 1000 V a.c. and 1500 V d.c. is defined in identical fashion by the standards EN 605 29 - IEC 529 it comprises the letters IP followed by two character numerals:









The first character numeral indicated the degree of protection provided by the enclosure with respect to persons, also to the equipment inside the enclosure.

The first character numeral:
protection against solid substances

IP	Description
0	Non-protected
1	 Protected against solid objects greater than 50mm
2	 Protected against solid objects greater than 12.5mm
3	 Protected against solid objects greater than 2.5mm
4	 Protected against solid objects greater than 1.0mm
5	 Dust-protected
6	 Dust-tight

The second character numeral indicated the degree of protection provided by the enclosure with respect to harmful ingress of water; a third character may be used to indicate mechanical strength. An x signifies that no test has been carried out.

The second character numeral:
protection against liquid substances

IP	Description
0	Non-protected
1	 Protected against dripping water
2	 Protected against dripping water when tilted up to 15°
3	 Protected against spraying water
4	 Protected against splashing water
5	 Protected against water jets
6	 Protected against heavy seas
7	 Protected against the effect of immersion 15 cm
8	 Protected against submersion m

Additional letter (in option)

Protection of people against access to dangerous parts


	Description
A	Protected against access of the back of the hand
B	Protected against access of a finger
C	Protected against access of a tool - ø 2.5mm
D	Protected against access of a tool - ø 1mm

Additional letter (in option)


Specific information on the product

	Description
H	High voltage material
M	Movements during water test
S	Stationary during water test
W	Bad weather


One way switch




Two way switch




Marked BELL switch




Marked PRESS switch




Intermediate switch



Fan control




Audio switch




Dimmer switch


1. One way connection




2. Two way connection



Do not disturb and please clean the switch (inside the door) / Do not disturb and please clear the instructions and the doorbell switch (outside the door)




RJ45 Computer module cable diagram EIA/TIA 568B



RJ45 Jack pin.
EIA/TIA 568B EIA/TIA 568A

1 White/Orange	White/Green
2 Orange	Green
3 White/Green	White/Orange
4 Blue	Blue
5 White/Blue	White/Blue
6 Green	Orange
7 White/Brown	White/Brown
8 Brown	Brown


RJ11 Telephone plug-in module cable diagram




RJ11 Jack pin.

2 Blue/White
3 White/Blue
4 White/Red
5 Red/White


Key card Direct load



Key card Connected load through contactor



Residential application



Home garden / dining room


Product catalog

200W Infrared sensor switch fire control	1
13A single switched socket	2
13A twin socket	2
13A single switched socket + 2 x USB chargers	1
16AX 1 gang 1 way switch	1
16AX 2 gang 2 way switch	1
16AX 2 gang 1 way switch	1
RJ11 outlet, 1 mod	1
RJ45 cat6 outlet	1
TV outlet, 1 mod	1
2 gang horizontal frame	2
5 gang horizontal frame	1

Restaurant / kitchen

Product catalog

13A single switched socket	8
13A twin socket	2
13A single switched socket + 2 x USB chargers	1
16AX 2 gang 2 way switch	1
16AX 2 gang 1 way switch	1
TV outlet, 1 mod	1
3 gang horizontal frame	2



Bedroom / dressing room / study room

Product catalog

10AX 1 gang intermediate	
13A twin socket	
13A single switched socket + 2 x USB chargers	
16AX 2 gang 1 way switch	
RJ11 outlet, 1 mod	
RJ45 cat6 outlet	
TV outlet, 1 mod	
Sleeping light	

QTY

2
2
1
1
1
1
1
2

Bathroom / balcony


Product catalog

16AX 2 gang 1 way switch	
13A single switched socket	
Blank plate	
WA cover (IP55)	

QTY

1
2
4
2

Hotel application




Entrance / Bar counter

Product catalog

- 4A DND & MUR indicator w/ bell switch
- 16A key tag RFID
- 16AX 1 gang 1 way LED switch
- 16AX 2 gang 2 way LED switch
- 13A single switched socket

Bed			
QTY	Product catalog	QTY	
1	16AX 2 gang 1 way w/ LED switch	1	
1	13A single switched socket, 2 x USB chargers	1	
1	13A single switched socket	2	
1	40-500W 2 way dimmer	2	
3	RJ11 outlet, 1 mod	1	
	RJ45 ca5e outlet	1	
	Sleeping light	1	



Desk

Product catalog

16AX 2 gang 1 way w/ LED switch
 HDMI+VGA
 13A single switched socket + 2 x USB chargers
 13A single switched socket
 RJ11 outlet, 1 mod
 RJ45 cat6 outlet

QTY

1
 1
 1
 2
 1
 1

Bathroom


Product catalog

16AX 2 gang 1 way w/ LED switch
 Shaver socket
 Sleeping light
 SOS emergency switch
 6W Audio switch
 13A single switched socket
 RJ11 outlet, 1 mod
 WA cover (IP55)

QTY

2
 1
 1
 1
 1
 3
 1
 4

Office application



Single office


Product catalog

16AX 1 gang 1 way switch	8
16AX 2 gang 2 way switch	16
13A single switched socket	48
13A single switched socket + 2 x USB chargers	8
RJ45 cat6 outlet	16
HDMI+VGA	8
6A Audio switch	8
2 gang horizontal frame	16
3 gang horizontal frame	16

Open area office

Product catalog

16AX 1 gang 1 way switch	6
16AX 3 gang 1 way switch	10
16AX 4 gang 1 way switch	8
13A single switched socket	100
RJ11+RJ45 ca5e outlet	50
6A Audio switch	8
2 gang horizontal frame	6
3 gang horizontal frame	54



Meeting room

Product catalog

16AX 1 gang 1 way switch	2
16AX 2 gang 1 way switch	4
16AX 3 gang 1 way switch	4
13A single switched socket	20
RJ11 outlet	2
RJ45 ca6 outlet	12
HDMI+VGA	1
3 gang horizontal frame	6
4 gang horizontal frame	54

Public area:

reception/ corridor/ pantry/ washroom

Product catalog

Sleeping light	12
13A single switched socket	12
200W Infrared sensor switch fire control	16
WA cover (IP55)	4

QTY

12
12
16
4

Success cases

The courage to try to innovate in architectural design; the design of excellence always brings together a lot of ideas; the pursuit of the ultimate detail and the admiration of superior quality. Today, whether in Munich, Berlin and Hamburg, or in Bolzano, Madrid and Seoul, these ideas can be traced in any building in the world. It is no coincidence that Hager switches and systems can be found in all of these places.

China

Sofitel Shenyang Lido, Shenyang
New World Beijing Hotel, Beijing
Fairmont Beijing, Beijing
Marriott Nanjing South Hotel, Nanjing
Grand Hyatt, Hangzhou
Park Hyatt Ningbo Resort & Spa, Ningbo
The Peninsula, Shanghai
Le Royal Meridien Hotel, Shanghai
Swissôtel Grand Shanghai, Shanghai
Mandarin Oriental Pudong, Shanghai
Sofitel Shanghai Sheshan Oriental, Shanghai
JW Marriott, Hangzhou
Four Points by Sheraton Bijie, Guizhou
Kempinski Hotel, Yinchuan
New World Wuhan Hotel Wuhan
Mandarin Oriental Hotel Guangzhou
Hyatt Place Shenzhen Airport, Shenzhen
The Ritz-Carlton, Shenzhen
InterContinental, Shenzhen
Swissôtel, Foshan
Shangri-La's Sanya Resort & Spa, Hainan

Hong Kong & Macau

Sheraton Hotel Tung Chung
Island Shangri-La, Hong Kong
Penta Hotel
Hotel ICON
Royal Plaza Hotel
Ritz Carlton Hotel
Best Western Hotel (Causeway bay & Tsim Sha Tsui)
Harbour Grand Hong Kong
Hyatt Regency Hotel
Harbourview Horizon Hotel
Royal View Hotel
Grand Lisboa Macau
Studio City Macau
Galaxy Macau

Singapore

Grand Hyatt Hotel
Goodwood Park
Park Regis
Ramada & Days Hotel Singapore at Zhongshan Park
Hotel Fort Canning

Malaysia

Genting Hotel, Genting Highlands
JW Marriott Hotel, Kuala Lumpur
WEIL Hotel Ipoh, Perak
Alila Bangsar Kuala Lumpur, Kuala Lumpur
Hilton Garden Inn Puchong, Selangor
Alwaqf Hotel, Kelantan
Kimberley Hotel, Penang
Iconic Hotel, Penang
VE Hotel & Residence, Bangsar South, Kuala Lumpur

Indonesia

Westin Hotel, Jakarta
Courtyard by Marriott, Bali
Fairfield by Marriott Sunset Road, Bali
The Ritz-Carlton, Bali Resort & Spa, Bali

Vietnam

Novotel Nha Trang
Sealink Phan Thiet
Sheraton Da Nang
Radison Blu Cam Ranh
Movenpick Cam Ranh
Melia Cam Ranh
Hanoi Hotel

India

Taj Palace, Mumbai
Hyatt Place, Hyderabad
Ritz Carlton Pune, Pune
Lemon Tree, 3 hotels (Udaipur, Dehradun, Kolkata)
Fairfield Marriott Kolkata, Kolkata

Europe

Hotel Sacher, Vienna
Hotel Lux Alpinae, St. Anton am Arlberg
Hotel Schloss Elmau, Elmau
Vigilius Mountain Resort, Lana
Hotel Puerta l'America, Madrid
Lloyd Hotel, Amsterdam
Zentrum für Virtuelles
Engineering ZVE, Stuttgart
Herzogin Anna Amalia Bibliothek, Weimar
minimum bulthaup, Berlin
PrivatHaus, Berlin
Hyatt Regency, Istanbul
i li Marriott, Istanbul
Sheraton Ate ehir, Istanbul
Swissôtel, Istanbul
Le Meridien, Istanbul
Hilton, Izmir
Crowne Plaza, Istanbul

Other Countries

Sedona Hotel, Mandalay, Myanmar
Four Seasons Hotel, Seychelles
Makati Shangri-La Hotel, Manila





Hager Dream



Hager Silhouette



Berker R.1



Berker R. Classic



hagerblu visage



Berker B.IQ



Hager golf



Hager witty



Hager Design turns technical products into familiar friends.



International designer Erwin van Handenhoven has been working with Hager since 2000 and his designs have repeatedly won international design awards. Erwin became the product design director of Hager Group in 2013, focusing on shaping the future of Hager products and brands, making Hager design an international vane.

Before we start designing a new product, we think about the people it is going to serve. Will it assist or entertain, observe or protect, save time or save energy? Ideally, whatever it does, users will feel it is a reliable "friend". We need to know how to connect with people on an emotional level, to ensure that in return they feel connected to our products.

Design links exquisite emotions to great usability and quality. How to illustrate this better than through this new HAGER range? I designed it with special care to become a real trendsetter for good taste. We know that the Asian continent is constantly raising his design sensibility and quality expectations. It is exciting to create in this particular context where tradition and change operate together. This new design range will upgrade the standard of living in a clearly visible way. Hope you enjoy it as much as I do.

Erwin van Handenhoven

Corporate Design Director of Hager Group
Hager Group Design Director



Hager Electro GmbH Co. KG

Zum Gunterstal
66440 Blieskastel
Germany

Hager Electro S.A.S.

132, Boulevard d'Europe BP 3
67215 Obernai Cedex
France

Hager Middle East FZE

Office 222-227, Building A4
Dubai Digital Park, Dubai Silicon Oasis
P.O. Box 61056, Dubai
United Arab Emirates

Tel: (+971) 4 510 5300
Fax: (+971) 4 425 1598

Hager Qatar QFZ LLC

Office 3202, Level 2, Wing 3,
Business & Innovation Park
Qatar Free Zone
Ras Bu Fontas
PO Box 31830
Doha,
Qatar.

Tel: (+974) 55682915

hager-me.com