Hager Dream wiring accessories

live your Dream







:hager

Milestones of Hager wiring accessories





1919

Berker Brothers began to manufacture the first batch of rotary switches in Schalksmühle. Every detail was as simple, elegant, and functional as all Berker's other subsequent models.



Traditionally, water-proof switches are made of cast resin or ceramics. Therefore, Berker's molded plastics rotary switch is a real innovation. The threads of the rotary switch are pressed into the top of the gland cover and grease cavity seals are installed on the axle. This type of switches features optimal waterproof performance. Its basic design features remained unchanged for decades of years.



1966

Although it seems quite natural today, dating back to 1966, the launch of a switch equipped with a dismountable switch cover that can be backfilled after the completion of the painting engineering indicated a significant innovation and great progress in terms of convenience. Moreover, since the switch cover is easy to change, many of the 1966 rocker switches are still in good keep today and can still work normally.



1980

The combination of circle and square was one of our most successful products in the grim technical environment in the 1980s.



1996

'Twinpoint' design has interchangeable decorative rings, which provides all kinds of design possibilities



1928

Form + Function: When Bauhaus began to carry this concept forward, Berker Brothers have turned to the famous architect Louis Henri Sullivan's design concept. Functional and perfect design combined with reliable technology— Berker's switches already had all the elements that a product needs to become classic. These products later became classic indeed.



1957

The cover of this type of switch is as colorful as any of the modern works of art—That is why this colorful sample is called 'Chagall'.



1972

A big success, where modularization is used, the first type of stainless all-metal switch— Another

real innovation.



1983

An expert to deal with difficult tasks: 'ISO-Panzer' has excellent waterproof and shockproof performances excellent waterproof and shockproof performances



1999

TS series can not only assist in creating special lighting effect, but can also combine KNX system for operating the complete smart home system.



2003

Full ranges included system 8000, 9000, 9088 metal ranges for Asia launched.



2008

The greatest feature of TS Crystal Ball is its glittering Swarovski crystal and sensitive optical reflection sensor, very charming.



2009

Touch of style as

equipped with large

rocker and blue LED

system 10088

indication.

2016

Berker Q.7 not only highlights its form, functions, and craftsmanship, but also lifts architectural individuality and material application to a higher level.



2020

Hager Dream, Hager Inspire, Hager Muse with best-in-class aesthetics design, quality and full functions to answer all needs.



2004

Intelligence is a kind of beauty. Undoubtedly, B.IQ looks very beautiful: The first type of smart and fashionable home control unit in the world indicates the arrival of the new era of comfort.



2007

Only by touching... That is the artistic state to start to control a room. Technical progress makes it possible for us to combine minimalism with modern technology and create a new exchange mode.



2011

R.1 series explains its design of round angle of the excircle in its unique way. It has a soft framework outline and all kinds of functional versions. It is a good choice for all residential and decoration projects.



2013

stylea with slim and nice profile large rocker provided affordable option.




2018

Dream series, designed by the European designer, Erwin van Handenhoven, a winner of many international awards, bring elegant life experience to customers.

Dream with ambition

Frameless design

The ultra-slim, frameless design allows the switch to be integrated into the wall; the simple and large panel makes the contact easy, and each touch creates the most pleasant moment.



Hidden LED

Soft and discrete LED light to locate the switch as soon as you enter the room. No need to feel your way in the dark. Guided by the LED light, experience the convenience and safety.



Multiple choices of color for your switch

Pursue uniqueness and elegance, white, elegant gold, interstellar grey, noble bronze and knight black, the color tone personifies the style and poise.



Multiple choices of color for the switch ring

Details are carefully deliberated in the design. Ultra-slim panel with changeable colored ring is trendy and stylish.



Expert tips



01

Frameless design

The ultrathin and frameless appearance design makes the switch integrate with the wall into an integral whole; the simple but huge rocker makes contact very easy, and each touch creates the most touching moment.



04

Noise reduction design

Noise reduction is designed for the large switch panel, which embodies the sound and hand feeling of the products imported from Europe. The design idea from multi-dimensions such as impression, light perception, sense of touch, and phonoreception makes the large rocker perfect.



07

Color-changeable switch ring The switch rings of Dream series can change colors to match the interior decoration as you like, providing more possibilities for the overall design.



02

Hidden LED Soft and distinguishable LED light, you can find where the switch is located as soon as you enter the room, and you needn't feel your way in the dark to get up in the night. Guided by LED light, you will experience convenience and safety.



05

U type screwed terminals Capacity of terminal can fit 3 x 4mm² flexible/ rigid wire. However, it is easy to wiring, high efficient for installation.



03

Identification for power

humanized delayed power off is designed, which save power in a smart way. The insert tag switch has LED indicator, which makes it easy for you to find the slot in the dark. After power on, the indicator will turn off automatically.



06

Beehive-like support Beehive structure has the advantages of super-strong intensity and light weight. It is accurately used for the installing support of the product, which makes it more firm, durable, and not deformed over time.





08

IP55 waterproof box

The integrated production makes the waterproof and dustproof functions reach the high waterproof level of IP55. The design of a transparent large space box provides more space for the power cable to turn naturally, realizing real waterproof at power consumption.

09

Safety and stability The international standard rated current of switch is 16AX, which ensures safer and more stable use of the switch.





10

Shutter

Having safety awareness all the time comes from the care for every family member. The socket panel is designed with child lock. Source isolating safety shutter is installed at the jacks to prevent children from putting their single finger in. It can completely block current.

11

Surge protection capability The surge capability of electronic products can reach 2500V, it is 2.5 times higher than standard.



12

Monobloc rocker & frame design Rocker and the frame can be taken out by one time only, easy for installation. This is a perfect alignment of rockers all the time.



13

USB charger

4.2A, 5V charger is suitable for all kinds of electronic devices (1 type C + 2 type A). No need for extra charger, can be easily charged via USB cable, it also can be used for charging 3 devices at the same time.



14

Certified by British Nemko The shaver socket is certified by British Nemko. Grade II safety isolating transformer is used, which makes transformation safer and products more durable.



15

Dust-protection Cover Dust-protection cover is supplied for each product. It can be used for protecting the dust during decorating, keeping the product clean.



16

Ensuring communication quality The network socket ensures communication quality. It is certified by UL lab and ensures high-quality communication.



17

Eco-packaging We adhere to environmental philosophy all the time and won international iF design award for the packaging.



18

Designed by European master Designed by Erwin van Handenhoven, who has won many international awards.

Hager Dream series





Hager Dream series	Page
Wall switches	18
Dimmer and fan controller switches	19
Double pole control switches	20
Connection unit	20
13A socket outlets	21
Communication and data	22
Hotel range	23
Others	24
Product standard	25
Ingress protection	28
Circuit diagram	29
Application	32
Success cases	38

Hager Dream Wall switches



 Complies v IEC 60669- CB certifica 'AX' rated - for fluoresc 	-1 ate - No need to derate	 10 AX (100W Self Ballasted Lamp 16 AX (200W Self Ballasted Lamp Supplied with M3.5 x 24 long fixing screws) 3 x 1.5 2 X 4.0) - Two w		n be	 Terminal markings denote: L1 = one way L2 = two way C = common Material: Polycarbonate 		
		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold
		Large dolly switch 16AX, 1 gang 1 way	10	WGDL111	WGDL111IG	WGDL111NB	WGDL111KB	WGDL111EG
		16AX, 1 gang 2 way	10	WGDL112	WGDL112IG	WGDL112NB	WGDL112KB	WGDL112EG
WGDL111 WGDL112	WGDL121 WGDL122	16AX, 2 gang 1 way	10	WGDL121	WGDL121IG	WGDL121NB	WGDL121KB	WGDL121EG
NGDETTZ	WGDE122	16AX, 2 gang 2 way	10	WGDL122	WGDL122IG	WGDL122NB	WGDL122KB	WGDL122EG
		16AX, 3 gang 1 way	10	WGDL131	WGDL131IG	WGDL131NB	WGDL131KB	WGDL131EG
		16AX, 3 gang 2 way	10	WGDL132	WGDL132IG	WGDL132NB	WGDL132KB	WGDL132EG
WGDL131 WGDL132	WGDL141 WGDL142	16AX, 4 gang 1 way	10	WGDL141	WGDL141IG	WGDL141NB	WGDL141KB	WGDL141EG
		16AX, 4 gang 2 way	10	WGDL142	WGDL142IG	WGDL142NB	WGDL142KB	WGDL142EG
		Large dolly switch with LE 16AX, 1 gang 1 way	D 10	WGDL111N	WGDL111NIG	WGDL111NNE	8 WGDL111NKB	WGDL111NE
		16AX, 1 gang 2 way	10				WGDL112NKB	
NGDL111N NGDL112N	WGDL121N WGDL122N	16AX, 2 gang 1 way	10				WGDL121NKB	
		16AX, 2 gang 2 way	10				WGDL122NKB	
		16AX, 3 gang 1 way	10				WGDL131NKB	
WGDL131N WGDL132N		16AX, 3 gang 2 way	10	WGDL132N	WGDL132NIG	WGDL132NNE	WGDL132NKB	WGDL132NE
		Large dolly switch 10AX, 1 gang, intermediate	10	WGDL113	WGDL113IG	WGDL113NE	WGDL113KB	WGDL113E
WGDL113	WGDL111B	10A, 1 gang, bell switch mark Bell symbol	10	WGDL111B	WGDL111BIG	WGDL111BNE	WGDL111BKB	WGDL111BE
		Press switch 10A, 1 gang 10 WGD	L111F	9 WGDL11	1PIG WGDL	.111PNB W0	GDL111PKB W	/GDL111PE(

10A, 2 gang 10 WGDL121P WGDL121PIG WGDL121PNB WGDL121PKB WGDL121PEG

10A, 3 gang 10 WGDL131P WGDL131PIG WGDL131PNB WGDL131PKB WGDL131PEG

WGDL111P WGDL121P WGDL131P



- Complies with IEC 60669-2-1		 Supplied wi long fixing s Capacity of 3 x 1.5 mm² 	crews	i	- Material: Poly	/carbonate		
		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref Knigt Black	Cat. Ref Elegant Gold
		Dimmer 40-500W single, 2 way	6	WGDEDR500	WGDEDR500IG	WGDEDR500NB	WGDEDR500KB	WGDEDR500EG
WGDEDR500 V	WGDEFR250	Fan control 250VA, single	6	WGDEFR250	WGDEFR250IG	WGDEFR250NB	WGDEFR250KB	WGDEFR250EG

Hager Dream Double pole control switches

- Complies with IEC 60669-1 CB certificate		 20 AX (250W Self Ballasted Lamp (SBL)) Supplied with M3.5 x 25 mm long fixing screws 			- Capacity of e 20AX L, N, E: 2 x 4 32A, 45A L, N : 2.5 mm E x 2 : 2.5 mm	• mm² n²~ 16 mm²	- Material: Polycarbonate	
				: Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold
		DP switch 20AX 1 gang		WGDL2D1	WGDL2D1IG	WGDL2D1NB	WGDL2D1KB	WGDL2D1EG
WGDL2D1	WGDL2D2	20AX 2 gang	8	WGDL2D2	WGDL2D2IG	WGDL2D2NB	WGDL2D2KB	WGDL2D2EG
		DP switch witł 20AX 1 gang) WGDL2D1N	WGDL2D1NIG	WGDL2D1NNB	WGDL2D1NKB	WGDL2D1NEG
		20AX 2 gang	8	WGDL2D2N	WGDL2D2NIG	WGDL2D2NNB	WGDL2D2NKB	WGDL2D2NEG
WGDL2D1N WGDL2D12N	WGDL2D2N	20AX 1 gang 2 way	8	WGDL2D12N	WGDL2D12NIG	WGDL2D12NNB	WGDL2D12NKB	WGDL2D12NEG
		Control swite	ch wi	ith LED				
		32A DP	8	WGDR32D1	WGDR32D1IG	WGDR32D1NB	WGDR32D1KB	WGDR32D1EG
-	-	45A DP	8	WGDR45D1	WGDR45D1IG	WGDR45D1NB	WGDR45D1KB	WGDR45D1EG
WGDR32D1	WGDR45D1							

Hager Dream Connection unit



- 25A Connection units BS 5733 IEC 60998-1 IEC 60998-2-1	- Fused connection units complies with BS 1363-4			25A L, N, E: 4 x 2	each terminal: 2.5 mm² or 2 x 4 mm x 6 mm²	·	- Material: polycarbonate		
	- Supplied w long fixing s			13A FCU L, N : 3 x 4.0 E : 2 x 4.0					
	Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold		
	Connection 25A with flex outlet	unit 12	WGDR25	WGDR25IG	WGDR25NB	WGDR25KB	WGDR25EG		



....

WGDR13N2



WGDR13N



WGDR13SN5 WGDR13SN

WGDR13N5

WGDR13SN2

Fused conne	ction	unit				
2A fused w/ neon + flex outlet	10	WGDR13N2	WGDR13N2IG	WGDR13N2NB	WGDR13N2KB	WGDR13N2EG
5A fused w/ neon + flex outlet	10	WGDR13N5	WGDR13N5IG	WGDR13N5NB	WGDR13N5KB	WGDR13N5EG
13A fused w/ neon + flex outlet	10	WGDR13N	WGDR13NIG	WGDR13NNB	WGDR13NKB	WGDR13NEG
2A switched fused w/ flex outlet w/ neor	10 า	WGDR13SN2	WGDR13SN2IG	WGDR13SN2NB	WGDR13SN2KB	WGDR13SN2EG
5A switched fused w/ flex outlet w/ neor		WGDR13SN5	WGDR13SN5IG	WGDR13SN5NB	WGDR13SN5KB	WGDR13SN5EG
13A switched fused w/ flex outlet	10	WGDR13SN	WGDR13SNIG	WGDR13SNNB	WGDR13SNKB	WGDR13SNEG

w/ neon

:hager

Hager Dream 13A socket outlets

- Complies with BS 1363-2 SS 145-2			 Supplied with M3.5 x 25 mm long fixing screws Capacity of each terminal: 			urrent ⁄Iax) r design of	- Material: Polycarbonate	
		L, N, E : 3 X 2.5 mm² or 2 X 4.0 mm²			switched sock clear red 'on'			
		Description		Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold
		13A single	10	WGDS113	WGDS113IG	WGDS113NB	WGDS113KB	WGDS113EG
WGDS113	WGDS113S	13A single switched	10	WGDS113S	WGDS113SIG	WGDS113SNB	WGDS113SKB	WGDS113SEG
. 0	E	13A single DP switched	10	WGDS113SDP	WGDS113SDPIG	WGDS113SDPNB	WGDS113SDPKB	WGDS113SDPEG
WGDS113SDP	WGDS113SUSB	13A single switched 2 x USB charge	8 ers	WGDS113SUSB	WGDS113SUSBIG	WGDS113SUSBNB	WGDS113SUSBKB	WGDS113SUSBEG
. 00	-	13A twin switched	10	WGDS213S	WGDS213SIG	WGDS213SNB	WGDS213SKB	WGDS213SEG
WGDS213S		13A twin DP switched	10	WGDS213SDP	WGDS213SDPIG	WGDS213SDPNB	WGDS213SDPKB	WGDS213SDPEG
WGDS213SDP	-	13A twin switched 2 x USB char	10 gers	WGDS213SUSB	WGDS213SUSBIG	WGDS213SUSBNB	WGDS213SUSBKB	WGDS213SUSBEG

Hager Dream Communication and data



- Supplied with M3.5 x 25 mm long fixing screws

- Material: Polycarbonate

		Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold
		RJ11 outlet 1 mod	10	WGDT1RJ	WGDT1RJIG	WGDT1RJNB	WGDT1RJKB	WGDT1RJEG
		2 mod	10	WGDT2RJ	WGDT2RJIG	WGDT2RJNB	WGDT2RJKB	WGDT2RJEG
VGDT1RJ	WGDT2RJ							
		RJ45 cat6 օւ 1 mod	itlet 10	WGDT1RJ6	WGDT1RJ6IG	WGDT1RJ6NB	WGDT1RJ6KB	WGDT1RJ6E0
VGDT1RJ6	WGDT2RJ6	2 mod	10	WGDT2RJ6	WGDT2RJ6IG	WGDT2RJ6NB	WGDT2RJ6KB	WGDT2RJ6E0
		RJ45 cat5e c 1 mod 2 mod	outlet 10 10	WGDT1RJ5 WGDT2RJ5	WGDT1RJ5IG WGDT2RJ5IG	WGDT1RJ5NB WGDT2RJ5NB	WGDT1RJ5KB WGDT2RJ5KB	WGDT1RJ5E0 WGDT2RJ5E0
WGDT1RJ5	WGDT2RJ5							
8 8 1	•	RJ11 + RJ45 2 mod	cat5e 10	e outlet WGDT2RJRJ5	WGDT2RJRJ5IG	WGDT2RJRJ5NB	WGDT2RJRJ5KB	WGDT2RJRJ5E
VGDT2RJRJ5 VGDT2RJRJ6	WGDT2TVRJ5	RJ11 + RJ45 2 mod	cat6 10	outlet WGDT2RJRJ6	WGDT2RJRJ6IG	WGDT2RJRJ6NB	WGDT2RJRJ6KB	WGDT2RJRJ6E
•	- - -	TV inlet/outle 2 mod	et + R. 10		WGDT2TVRJ5IG	WGDT2TVRJ5NB	WGDT2TVRJ5KB	WGDT2TVRJ5E
VGDT1TV	WGDT1TVF	TV inlet/outle 1 mod	et 10	WGDT1TV	WGDT1TVIG	WGDT1TVNB	WGDT1TVKB	WGDT1TVEG
		TV outlet, F t 1 mod	t ype 10	WGDT1TVF	WGDT1TVFIG	WGDT1TVFNB	WGDT1TVFKB	WGDT1TVFE

Subject to change without prior notice

:hager

- Complies with IEC 60669-1 IEC 60669-2-1 IEC 62368-1 (USB)		- 16 AX (200W Self B	- 16 AX (200W Self Ballasted Lamp (SBL))			- Supplied with M3.5 x 25 mm long fixing screws		- Material: Polycarbonate	
		Description		Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold	
b ø	de la	16AX DND & MUR with LED (Indoor)	8	WGDHDC	WGDHDCIG	WGDHDCNB	WGDHDCKB	WGDHDCEG	
WGDHDC	WGDHBD	4A DND & MUR indicato w/ bell switch		WGDHBD	WGDHBDIG	WGDHBDNB	WGDHBDKB	WGDHBDEG	
		16A key tag - mechanical	6	WGDHKTM	WGDHKTMIG	WGDHKTMNB	WGDHKTMKB	WGDHKTMEG	
Ngdhktm Ngdhktrfid		16A key tag - RFID	6	WGDHKTRFID	WGDHKTRFIDIG	WGDHKTRFIDNB	WGDHKTRFIDKB	WGDHKTRFIDEG	
-	•	HDMI+VGA	10	WGDHHIVA	WGDHHIVAIG	WGDHHIVANB	WGDHHIVAKB	WGDHHIVAEG	
VGDHHIVA	WGDHRCASV	RCA+S-Vide	o 10	WGDHRCASV	WGDHRCASVIG	WGDHRCASVNB	WGDHRCASVKB	WGDHRCASVE	
- 8-8	• =	USB charger USB charger x 3 (4.2A)	's 8	WGDS3USB	WGDS3USBIG	WGDS3USBNB	WGDS3USBKB	WGDS3USBEC	
VGDS3USB	WGDHUSB35	USB + 3.5mr	n aud 10		WGDHUSB35IG	WGDHUSB35NB	WGDHUSB35KB	WGDHUSB35E	
•		Emergency	switcł 8	ו WGDEE1	WGDEE1IG	WGDEE1NB	WGDEE1KB	WGDEE1EG	
	WGDEA6	Audio switch 6W	6	WGDEA6	WGDEA6IG	WGDEA6NB	WGDEA6KB	WGDEA6EG	
VGDEE1									
VGDEE1	53	Sleeping ligh	n t 8	WGDHSL	WGDHSLIG	WGDHSLNB	WGDHSLKB	WGDHSLEG	

WGDHSR

Hager Dream Others



	Description	Pack qty.	Cat. Ref. White	Cat. Ref. Interstellar Grey	Cat. Ref. Noble Bronze	Cat. Ref Knight Black	Cat. Ref Elegant Gold
	Accommoda	ation p	late				
	1 gang	18	WGDVE2	WGDVE2IG	WGDVE2NB	WGDVE2KB	WGDVE2EG
WGDVE2							
	Blank plate 1 gang	20	WGDBP1	WGDBP1IG	WGDBP1NB	WGDBP1KB	WGDBP1EG
WGDBP1							
1 ⁴	WA covers IP55	40	XC9003				



	single size			
2	IP55 twin size	40	XC9004	

XC9004

:hager

Compliance with standards

Regulation 511-01-01 of BS 7671 : Requirements for Electrical Installations, IEE Wiring Regulations Sixteenth Edition is of particular importance to specifiers and installers with respect to product standards.

Regulation 511-01-01 requires every item of equipment to comply with the relevant requirements of the applicable British Standard, or Harmonised Standard appropriate to the intended use of the equipment.

British Standards (BS)

The BSI (British Standards Institution) was the first national standards body in the world. There are now more than 100 similar organisations which belong to the International Organisation for Standardisation (ISO) and the International Electrotechnical Commission (IEC).

British Standards are drawn up by all those who have a particular interest in the subject i.e. manufacturers, users, research organisations, government departments and consumers. This work is co-ordinated by BSI staff, acting as secretaries to the committees where the work is done. All standards are made available for public comment before they are published.

Harmonised standards

A Harmonised standard is a European standard formally presented by CENELEC, to the European Commission and published in the commission's official journal. CENELEC is the Comite European de Normalisation Electrotechnique i.e. European Committee for Electrotechnical Standardisation.

BS 7671 part 2 defines a harmonised standard as a standard which has been drawn up by common agreement between national standards bodies notified to the European Commission by all member states and published under national procedures. The UK national standards body is the British Standards Institution. In the UK a harmonised standard will normally be published as a British Standard European Norm i.e. BS EN.

British Standard European Norm (BS EN)

CENELEC European standards are pre-fixed EN (European Norm). Adoption of the European Standard within the EC is mandatory and member countries of CENELEC are obliged to publish them unchanged. In the UK such standards are further endorsed with the additional prefix 'BS', for example BS EN 60669-1 : 1996 is the British Standard European Norm for Switches for household and similar fixed electrical installations.

Whilst a European Standard can be a direct replica of an IEC standard, discussions within CENELEC may result in the formulation of a standard which includes commonly agreed variations and Special National Conditions.

International Electrotechnical Commission (IEC)

Founded in 1906 the International Electrotechnical Commission (IEC) is the world organisation that prepares and publishes international standards for all electrical, electronic and related technologies. The membership consists of 60 participating countries, including all the worlds major trading nations and a growing number of industrialising countries.

Foreign national standards based on IEC standards are permitted to be used by BS 7671. However the specifier must verify that any differences between the foreign standard and the corresponding British Standard or Harmonised Standard does not result in any lesser degree of safety than that afforded by compliance with the British Standard. This assessment would probably need to be made by specialists.

Conclusion

BS 7671 (IEE Wiring Regulations) recognises equipment which complies with a British Standard or Harmonised Standard appropriate to the intended use of the equipment without the need for further qualification.

Hager products have always been designed and manufactured to a high standard to ensure compliance with the current British or Harmonised Standard. See the table below for further information.

Product description	BS / IEC number	Description
Switches	BS EN 60669-1 IEC 60669-1 CB certificate	Switches for household and similar fixed electrical installations
Indicators	BS 5733	General requirements for Electrical Accessories
Fused connection unit, cord outlets	BS 5733	Switches for household and similar fixed electrical installations with particular requirements for timedelay switches (TDS)
Dimmers	BS EN 60669-2-3	Switches for household and similar fixed electrical installations with particular requirements for timedelay switches (TDS)
Frames and plates	BS 5733	Switches for household and similar fixed electrical installations with particular requirements for timedelay switches (TDS)
10 /16 Amp Wall switch	BS EN 60669-1 IEC 60669-1 CB certificate	Switches for household and similar fixed electrical installations
Dimmer switches	BS EN 60669-2-1 IEC 60669-2-1	Electronic variable control switches (dimmer switches) for tungsten filament lighting
13 Amp Socket Outlets	BS 1363- 2 SS145-2	13A plugs, socket-outlets, adaptors and connection units
15 Amp Switched Socket	BS 546 SS472 MS1577	Specification. Two-pole and earthing-pin plugs, socket-outlets and socket-outlet adaptors
20 Amp D.P. Switches	BS EN 60669-1 IEC 60669-1 CB certificate	Switches for household and similar fixed electrical installations
13 Amp Fused Connection Unit	BS 1363-4	Specification for 13A fused connection units switched and unswitched
45 Amp D.P. Switches	BS EN 60669-1 IEC 60669-1 CB certificate	Switches for household and similar fixed electrical installations
45 Amp Cooker Control Unit	BS 4177	Cooker control units
Shaver Socket Outlet	BS EN 61558-2-5	General Requirements Isolating transformers and safety isolating transformers
	IEC 61558-2-5	Electromagnetic compatibility, immunity requirements for household CB certificate appliances tools and similar apparatus.
25 Amp/ Amp Flex Outlet Plate	BS 5733	General Requirements for Electrical Accessories
BS Batten	BS EN 61184 IEC 61184 BS EN 60238 IEC 60238	Home office shield are T2 rated
Ceiling rose	BS 67	
	1	

Objective of CE marking.

CE marking is a "technical passport" which indicates that a product conforms to all relevant directives which require CE marking, thus enabling the product to travel within the E.U.

A directive is a piece of mandatory European Legislation implemented by regulations in all member countries. Its purpose is to allow free movement of goods that are safe and fit for use into and within the European Union.

CE marking is not a quality mark and it does not indicate that any testing or certification has been carried out.

The marking.

CE marking is a statement by the manufacturer that the product complies with the essential requirements of all relevant Directives, notably in the area of technical safety and conformity assessment.

CE marking can appear on the product or packaging or documentation or combination thereof dependant upon which directive it has to comply with.

CE marking is a very specific graphical symbol and must be clearly separated from other marks.



Directives.

It is the responsibility of the manufacturer or his authorised representative who places the product onto the EC market to decide which Directive(s) apply and to ensure the CE marking is affixed by the dates stated in the relevant directive(s)

For the majority of Hager products only one directive is applicable this is referred to as the Low Voltage Directive. Where some products incorporate electronic devices the Low voltage Directive and the Electromagnetic Compatibility Directive are applicable.

The low voltage directive.

EC directives are requirements adopted by the European Council and published in the official journal of the European Communities and are addressed to the member states.

European Council Directive 73/23/EEC with an amendment 93/68/ EEC is known as the Low Voltage Directive.

The low voltage directive has been implemented into UK law by the "Electrical Equipment (Safety) Regulations 1994" and apply to all electrical / electronic equipment operating at a voltage of 50-1000 V a.c. or 75-1500 V d.c.. They do not apply to plugs, socket outlets and adapters which are covered by the Plugs and Sockets (Safety) Regulations 1994.

Relationship between the Electrical Equipment (Safety) Regulations, Harmonised standards and the IEE Wiring Regulations Sixteenth Edition.

The Electrical Equipment (Safety) Regulations requires electrical equipment to be safe. Electrical equipment which satisfies the safety provisions of Harmonised standards shall be taken to comply with this requirement, unless there are reasonable grounds for suspecting that the equipment does not so comply.

Regulation 511-01-01 of BS 7671 Requirements for Electrical Installations, IEE Wiring Regulations Sixteenth Edition requires every item of equipment to comply with the relevant requirements of the applicable British Standard, or Harmonised Standard appropriate to the intended use of the equipment. The Ingress Protection (IP) for all low voltage enclosures up to 1000 V a.c. and 1500 V d.c. is defined in identical fashion by the standards EN 605 29 - IEC 529 it comprises the letters IP followed by two character numerals:

The first character numeral indicated the degree of protection provided by the enclosure with respect to persons, also to the equipment inside the enclosure.

The first character numeral:

protection against solid substances

IP	Description	
0		Non-protected
1	[]	Protected against solid objects greater than 50mm
2		Protected against solid objects greater than 12.5mm
3		Protected against solid objects greater than 2.5mm
4		Protected against solid objects greater than 1.0mm
5	I	Dust-protected
6	3	Dust-tight

The second character numeral indicated the degree of protection provided by the enclosure with respect to harmful ingress of water; a third character may be used to indicate mechanical strength. An x signifies that no test has been carried out.

The second character numeral:

protection against liquid substances

IP	Description	
0		Non-protected
1	F	Protected against dripping water
2	, J	Protected against dripping water when tilted up to 15°
3	J	Protected against spraying water
4	Z	Protected against splashing water
5	• 5	Protected against water jets
6		Protected against heavy seas
7	15 cm	Protected against the effect of immer- sion
8	m F	Protected against submersion

Additional letter (in option)

Protection of people against access to dangerous parts

	Description
А	Protected against access of the back of the hand
В	Protected against access of a finger
С	Protected against access of a tool - ø 2.5mm
D	Protected against access of a tool - ø 1mm


Additional letter (in option)

Specific information on the product


	Description
Н	High voltage material
М	Movements during water test
S	Stationary during water test
W	Bad weather

:hager


One way switch




Two way switch




Marked BELL switch




Marked PRESS switch




Intermediate switch



Fan control




Audio switch




Dimmer switch


1. One way connection




2. Two way connection



Do not disturb and please clean the switch (inside the door) / Do not disturb and please clear the instructions and the doorbell switch (outside the door)



RJ45 Computer module cable diagram EIA/TIA 568B




RJ45 Jack pin. EIA/TIA 568B

EIA/TIA 568A

1 White/Orange White/Green 2 Orange Green 3 White/Green White/Orange 4 Blue Blue 5 White/Blue White/Blue 6 Green Orange White/Brown 7 White/Brown 8 Brown Brown

RJ11 Telephone plug-in module cable diagram




RJ11 Jack

RJ11 Jack pin.

2 Blue/White 3 White/Blue 4 White/Red 5 Red/White


:hager

Key card Direct load




Key card

Connected load through contactor



Residential application




Home garden / dining room

Product catalog	QTY
200W Infrared sensor switch fire control	1
13A single switched socket	2
13A twin socket	2
13A single switched socket + 2 x USB chargers	1
16AX 1 gang 1 way switch	1
16AX 2 gang 2 way switch	1
16AX 2 gang 1 way switch	1
RJ11 outlet, 1 mod	1
RJ45 cat6 outlet	1
TV outlet, 1 mod	1
2 gang horizontal frame	2
5 gang horizontal frame	1

Restaurant / kitchen

Product catalog	QTY
13A single switched socket	8
13A twin socket	2
13A single switched socket + 2 x USB chargers	1
16AX 2 gang 2 way switch	1
16AX 2 gang 1 way switch	1
TV outlet, 1 mod	1
3 gang horizontal frame	2



Bedroom / dressing room / study room oduct catalog D

0	TV	
U	1 Y	

2

1

1

1 1

1

2

QTY	Produc
2	16AX 2

16AX 2 gang 1 way switch 1 13A single switched socket 2 Blank plate 4 WA cover (IP55) 2


Product catalog
10AX 1 gang intermediate
13A twin socket
13A single switched socket + 2 x USB chargers
16AX 2 gang 1 way switch
RJ11 outlet, 1 mod
RJ45 cat6 outlet
TV/ southed of uses of

- F
- TV outlet, 1 mod
- Sleeping light

Bathroom / balcony ct catalog

QTY

Hotel application




Entrance / Bar counter

Product catalog
4A DND & MUR indicator w/ bell switch
16A key tag RFID
16AX 1 gang 1 way LED switch
16AX 2 gang 2 way LED switch
13A single switched socket

Bed

QTY

Product catalog	QTY
16AX 2 gang 1 way w/ LED switch	1
13A single switched socket, 2 x USB chargers	1
13A single switched socket	2
40-500W 2 way dimmer	2
RJ11 outlet, 1 mod	1
RJ45 ca5e outlet	1
Sleeping light	1



Desk


Product catalog

16AX 2 gang 1 way w/ LED switch	
HDMI+VGA	
13A single switched socket + 2 x USB chargers	
13A single switched socket	
RJ11 outlet, 1 mod	
RJ45 cat6 outlet	

Bathroom

Product catalog	QTY
16AX 2 gang 1 way w/ LED switch	2
Shaver socket	1
Sleeping light	1
SOS emergency switch	1
6W Audio switch	1
13A single switched socket	3
RJ11 outlet, 1 mod	1
WA cover (IP55)	4

Office application




Product catalog	Prod	uct	cata	log
-----------------	------	-----	------	-----

16AX 1 gang 1 way switch	8
16AX 2 gang 2 way switch	16
13A single switched socket	48
13A single switched socket + 2 x USB chargers	8
RJ45 cat6 outlet	16
HDMI+VGA	8
6A Audio switch	8
2 gang horizontal frame	16
3 gang horizontal frame	16

QTY

Product catalog	QTY
16AX 1 gang 1 way switch	6
16AX 3 gang 1 way switch	10
16AX 4 gang 1 way switch	8
13A single switched socket	100
RJ11+RJ45 ca5e outlet	50
6A Audio switch	8
2 gang horizontal frame	6
3 gang horizontal frame	54



Meeting room Product catalog

Public area:

QTY

reception/ corridor/ pantry/ washroom		
Product catalog	QTY	
Sleeping light	12	
13A single switched socket	12	
200W Infrared sensor switch fire control	16	
WA cover (IP55)	4	

Success cases

The courage to try to innovate in architectural design; the design of excellence always brings together a lot of ideas; the pursuit of the ultimate detail and the admiration of superior quality. Today, whether in Munich, Berlin and Hamburg, or in Bolzano, Madrid and Seoul, these ideas can be traced in any building in the world. It is no coincidence that Hager switches and systems can be found in all of these places.

China

Sofitel Shenyang Lido, Shenyang New World Beijing Hotel, Beijing Fairmont Beijing, Beijing Marriott Nanjing South Hotel, Nanjing Grand Hyatt, Hangzhou Park Hyatt Ningbo Resort & Spa, Ningbo The Peninsula, Shanghai Le Royal Meridien Hotel, Shanghai Swissôtel Grand Shanghai, Shanghai Mandarin Oriental Pudong, Shanghai Sofitel Shanghai Sheshan Oriental, Shanghai JW Marriott, Hangzhou Four Points by Sheraton Bijie, Guizhou Kempinski Hotel, Yinchuan New World Wuhan Hotel Wuhan Mandarin Oriental Hotel Guangzhou Hyatt Place Shenzhen Airport, Shenzhen The Ritz-Carlton, Shenzhen InterContinental, Shenzhen Swissôtel, Foshan Shangri-La's Sanya Resort & Spa, Hainan

Hong Kong & Macau

Sheraton Hotel Tung Chung Island Shangri-La, Hong Kong Penta Hotel Hotel ICON Royal Plaza Hotel Ritz Cariton Hotel Best Western Hotel (Causeway bay & Tsim Sha Tsui) Harbour Grand Hong Kong Hyatt Regency Hotel Harbourview Horizon Hotel Royal View Hotel Grand Lisboa Macau Studio City Macau Galaxy Macau

Singapore

Grand Hyatt Hotel Goodwood Park Park Regis Ramada & Days Hotel Singapore at Zhongshan Park Hotel Fort Canning

Malaysia

Genting Hotel, Genting Highlands JW Marriott Hotel, Kuala Lumpur WEIL Hotel Ipoh, Perak Alila Bangsar Kuala Lumpur, Kuala Lumpur Hilton Garden Inn Puchong, Selangor Alwaqf Hotel, Kelantan Kimberley Hotel, Penang Iconic Hotel, Penang VE Hotel & Residence, Bangsar South, Kuala Lumpur

Indonesia

Westin Hotel, Jakarta Courtyard by Marriott, Bali Fairfield by Marriott Sunset Road, Bali The Ritz-Carlton, Bali Resort & Spa, Bali

Vietnam

Novotel Nha Trang Sealink Phan Thiet Sheraton Da Nang Radison Blu Cam Ranh Movenpick Cam Ranh Melia Cam Ranh Hanoi Hotel

India

Taj Palace, Mumbai Hyatt Place, Hyderabad Ritz Carlton Pune, Pune Lemon Tree, 3 hotels (Udaipur, Dehradun, Kolkata) Fairfield Marriott Kolkata, Kolkata

Europe

Hotel Sacher, Vienna Hotel Lux Alpinae, St. Anton am Arlberg Hotel Schloss Elmau, Elmau Vigilius Mountain Resort, Lana Hotel Puerta l'America, Madrid Lloyd Hotel, Amsterdam Zentrum für Virtuelles Engineering ZVE, Stuttgart Herzogin Anna Amalia Bibliothek, Weimar minimum bulthaup, Berlin Privathaus, Berlin Hyatt Regency, Istanbul i li Marriott, Istanbul Sheraton Ate ehir, Istanbul Swissôtel, Istanbul Le Meridien, Istanbul Hilton, Izmir Crowne Plaza, Istanbul

Other Countries

Sedona Hotel, Mandalay, Myanmyar Four Seasons Hotel, Seychelles Makati Shangri-La Hotel, Manila





Hager Dream





Hager Silhouette









Berker R. Classic





hagerblu visage





Berker B.IQ





Hager golf

reddot design award



Hager witty

reddot design award winer 2013

Hager Design turns technical products into familiar friends.



International designer Erwin van Handenhoven has been working with Hager since 2000 and his designs have repeatedly won international design awards. Erwin became the product design director of Hager Group in 2013, focusing on shaping the future of Hagrer products and brands, making Hager design an international vane.

Before we start designing a new product, we think about the people it is going to serve. Will it assist or entertain, observe or protect, save time or save energy? Ideally, whatever it does, users will feel it is a reliable "friend". We need to know how to connect with people on an emotional level, to ensure that in return they feel connected to our products. Design links exquisite emotions to great usability and quality. How to illustrate this better then through this new HAGER range ? I designed it with special care to become a real trendsetter for good taste. We know that the Asian continent is constantly raising his design sensibility and quality expectations. It is exciting to create in this particular context where tradition and change operate together. This new design range will upgrade the standard of living in a clearly visible way. Hope you enjoy it as much as I do.

Am

Erwin van Handenhoven

Corporate Design Director of Hager Group Hager Group Design Director

:hager

Hager Electro GmbH Co. KG Zum Gunterstal 66440 Blieskastel Germany

Hager Electro S.A.S. 132, Boulevard d'Europe BP 3 67215 Obernai Cedex France

Hager Middle East FZE Office 222-227, Building A4 Dubai Digital Park, Dubai Silicon Oasis P.O. Box 61056, Dubai United Arab Emirates

Tel: (+971) 4 510 5300 Fax: (+971) 4 425 1598

Hager Qatar QFZ LLC

Office 3202, Level 2, Wing 3, Business & Innovation Park Qatar Free Zone Ras Bu Fontas PO Box 31830 Doha, Qatar.

Tel: (+974) 55682915

hager-me.com